



Southwire™

ENT CONDUIT REELS

FEATURES

- Electrical Nonmetallic Tubing (ENT) reels
- UV rated
- Suitable for concrete encasement
- Pull resistant
- Fire resistant
- Impact resistant
- Flexible enough to be bent by hand, tough enough to withstand crushing and breaking

APPLICATION

- Can be installed and concealed in floors, walls and ceilings
- May be installed and exposed in areas not subject to physical damage and where the building does not exceed three floors above grade

STANDARD MATERIAL

- Heavy duty impact resistant PVC



1622R



PART #	SIZE	FEET PER REEL	FEET PER PACK	WEIGHT/CASE (LBS.)	INNER DIAMETER	OUTER DIAMETER
1621R	1/2"	1500	1500	187	.578"	.84"
1622R	3/4"	1000	1000	167	.778"	1.05"
1623R	1"	750	750	158	1"	1.315"
1624R	1 1/4"	1000	1000	254	1.345"	1.66"
1625R	1 1/2"	750	750	252	1.574"	1.90"
1626R	2"	500	500	240	2.025"	2.375"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.