



# Metal Halide ED28

## MS320/BU/PS-37

320W Pulse Start

Super Metal Halide Lamp



- High luminous flux and long life
- Constant color performance
- Universal operating position
- Suitable for use in enclosed luminaires

<b>Item #</b>	MS320/BU/PS-37
<b>Product Code</b>	72810
<b>UPC Code</b>	751338076143
<b>Watts</b>	320
<b>Shape</b>	ED28
<b>Base</b>	E39 Mogul
<b>Finish</b>	Clear
<b>Color Temp</b>	4000
<b>Initial Lumens</b>	34,000
<b>Average Rated Life</b>	20,000
<b>MOL</b>	8.0"
<b>ANSI Code</b>	M132/E

Specifications are subject to change without prior notice.



[www.topaz-usa.com](http://www.topaz-usa.com)

**NY Office:** 925 Waverly Ave • Holtsville, NY 11742 • 800-666-2852 • Fax: 631-758-8026

**CA Office:** 225 Parkside Drive, San Fernando, CA 91340 • 888-551-2852 or 818-838-3123 • Fax: 888-690-2852 or 818-838-3102

**FL Office:** 2020 West 26th Street, Jacksonville, FL 32209 • 800-338-2852 • Fax: 772-778-5386