



**Southwire®**

# STEEL FISH TAPE

Southwire's steel fish tape reaches easily above ceilings, under carpets, and through walls to install wire. The fish tape is available in multiple lengths, extending your reach where a traditional fish tape can't.



**EASY PULLS**  
Specially treated steel fish tape for longer life and easier pulling

**RUGGED DESIGN**  
High impact, durable case for long lasting performance and use

**BETTER ACCURACY**  
Laser etched footage markings to help identify length of pull



**Southwire™**

TOOLS & EQUIPMENT

[BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.]

**1-855-SWTOOLS**  
**(855-798-6657)**



[Southwiretools.com](http://Southwiretools.com)



## Features & Benefits

- Available in the following lengths: 25', 50', 65', 125' and 240'
- Laser etched footage markings to help identify length of pull
- High impact, durable case for long lasting performance and use
- Specially treated steel fish tape for longer life and easier pulling

## ACCESSORIES

### FISH TAPE LEADER (FTFL13)

- Flexible 13" leader easily attaches to 1/8" steel fish tapes
- Assists in guiding steel fish tapes through conduit turns and bends

## Specifications

MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	MATERIAL	TAPE STYLE	TAPE WIDTH	TAPE LENGTH
FTS1/8-25	582802	1/8 In Fish Tape Steel 25' Steel	8.5"	7"	1"	13 oz	Steel	Flat	1/8"	25'
FTS1/8-50	582801	1/8 In Fish Tape Steel 50' Steel	11.5"	8.75"	1.13"	26 oz	Steel	Flat	1/8"	50'
FTS1/8-65	582800	1/8 In Fish Tape Steel 65' Steel	11.5"	8.75"	1.13"	38 oz	Steel	Flat	1/8"	65'
FTS1/8-125	582799	1/8 In Fish Tape Steel 125' Steel	17"	13"	1.75"	71 oz	Steel	Flat	1/8"	125'
FTS1/8-240	582798	1/8 In Fish Tape Steel 240' Steel	17"	13"	1.75"	118 oz	Steel	Flat	1/8"	240'
FTS1/4-25	582797	1/4 In Fish Tape Steel 25' Steel	8.5"	7"	1"	13 oz	Steel	Flat	1/4"	25'

MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	MATERIAL	DIA.	FITS	EYELET CAPACITY
FTFL13	582807	Fish Tape Leader 13"	14.25"	0.38"	0.25"	2 oz	Flexible Steel	3/16"	1/8" Steel Fish Tape	5 X 12 AWG Unstripped, 7 X 10 AWG Bare

