

In-Wall Speaker Cable; High-Strand Flexible Unshielded Cable CM/CL3



APPLICATIONS Interconnect amplifiers and speakers for Hi-End audio transmission in pro audio, stereo, and hi-fidelity systems. Highly flexible. Listed by UL for use in NEC power-limited circuits except those routed in risers or in plenums. Suitable for use in wet locations, indoor or light duty outdoor use.

CONSTRUCTION

A.) CONDUCTOR	Hi strand count, flexible stranded high conductivity bare copper
B.) INSULATION	Polypropylene low lower capacitance and clear audio response.
C.) COLOR CODE	2/C Black, Red. 4/C Black, Red, White, Green.
D.) SHIELDING	Unshielded
E.) ASSEMBLY	Cabled, with ripcord, and jacketed.
F.) JACKET	Smooth, round, flexible PVC.

COMPLIANCE

A.) FLAME TEST	UL 1685 (by UL) / CSA FT1
B.) CABLE TYPE / LEGEND	SEE TABLE
C.) VOLTAGE	300V
D.) TEMPERATURE	75C
E.) SUITABLE USE:	General purpose low voltage and power-limited systems' circuits to NEC Article 725 16 AWG IS also for communications circuits to NEC Article 800.
F.) QA	UL listed to UL 13, 444

FEATURES & OPTIONS: Available in 1000ft or 500 ft packages, reels, or pull-boxes where practicable.
Optional: other colors, jackets with extruded stripes, and composite cables for multiple services.

Stock #	DESCRIPTION	AWG	#COND	STRANDS	COND	SHIELD	Rating	NOM. DIA. (Inches)	WEIGHT (Lb/Mft)
94562	16/2C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	16	2	65-STR	BC	N/S	CM/CL3	0.196	25.00
94564	16/4C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	16	4	65-STR	BC	N/S	CM/CL3	0.228	45.00
94542	14/2C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	14	2	105-STR	BC	N/S	CM/CL3	0.238	38.20
94544	14/4C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	14	4	105-STR	BC	N/S	CM/CL3	0.279	70.00
94762	16/2C CM/CL3 SUN RES	16	2	65-STR	BC	N/S	CM/CL3	0.192	29.00
94662	16/2C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	16	2	26-STR	BC	N/S	CM/CL3	0.198	25.20
94664	16/4C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	16	4	26-STR	BC	N/S	CM/CL3	0.230	45.10
94642	14/2C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	14	2	41-STR	BC	N/S	CM/CL3	0.242	37.70
94644	14/4C CM/CL3/FPL/PLTC DIRECT BURIAL SUN RES	14	4	41-STR	BC	N/S	CM/CL3	0.283	68.80
94722	12/2C CM/CL3 SUN RES	12	2	168-STR	BC	N/S	CM/CL3	0.278	67.30

Stock #	LEGEND
94562	SOUTHWIRE(R) SIGNAL(R) 94562 16 AWG 2/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1
94564	SOUTHWIRE(R) SIGNAL(R) 94564 16 AWG 4/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1
94542	SOUTHWIRE(R) SIGNAL(R) 94542 14 AWG 2/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1
94544	SOUTHWIRE(R) SIGNAL(R) 94544 14 AWG 4/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1
94762	SOUTHWIRE(R) SIGNAL(R) 94762 SOUNDSATIONAL 16 AWG 2/C C(ET)JUS TYPE CM/CL3 75(D)C AUDIO CABLE SUN RES -- CMH FT1
94662	SOUTHWIRE(R) SIGNAL(R) 94662 16 AWG 2/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1 P-07-KA120014-1-MSHA 300V
94664	SOUTHWIRE(R) SIGNAL(R) 94664 16 AWG 4/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1 P-07-KA120014-1-MSHA 300V
94642	SOUTHWIRE(R) SIGNAL(R) 94642 14 AWG 2/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1 P-07-KA120014-1-MSHA 300V
94644	SOUTHWIRE(R) SIGNAL(R) 94644 14 AWG 4/C C(ET)JUS TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES -- TYPE CMH FT1 P-07-KA120014-1-MSHA 300V
94722	SOUTHWIRE(R) SIGNAL(R) 94722 SOUNDSATIONAL 12 AWG 2/C C(ET)JUS TYPE CM/CL3 75(D)C AUDIO CABLE SUN RES -- CMH FT1

2/5/2021