

REEL MAC™ JACK

Sumner brings you the best built, best value reel jack you can buy. Reel Mac™ jacks are available in two styles. Style numbers 60 and 70 feature screw-type adjustment with large 1-1/2" screws and large, easy to use handles.

APPLICATIONS

- All steel constructions
- Rugged design for job site use
- Dependable Sumner quality

NO. 60 (#780941)

Screw-type telescoping Reel Jack for 26" to 56" diameter reels

NO. 70 (#780942)

Screw-type telescoping Reel Jack for 46" to 96" diameter reels

NO. 80 (#780943)

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use



ACCESSORY

Reel Mac Spindles Sumner spindles are designed to be used with Reel Mac reel jacks

PART #	DESCRIPTION	HEIGHT RANGE	LOAD CAPACITY	USE WITH SPINDLE	WEIGHT
780941	Reel Mac No. 60	13" - 27" (33 - 68 cm)	2,500 lbs (1,135 kg)	61	30 lbs (13.6 kg)
780942	Reel Mac No. 70	21" - 54" (53 - 137 cm)	2,500 lbs (1,135 kg)	71	51 lbs (23.1 kg)
780943	Reel Mac No. 80	28" - 45" (71 - 114 cm)	3,700 lbs (1,700 kg)	81	105 lbs (47.6 kg)