

Job Name/Title: _____

Model #: _____

Contractor: _____



Southwire™

CABLE TIES

NATURAL WHITE - INDOOR USE

FEATURES

- Operating temperature minimum -40°F to maximum 185°F
- Easy grab tip for pick up from flat surfaces
- Low insertion for quick installation
- High Yield Strength

APPLICATION

- Safely and easily secures wire bundles and harness components

STANDARD MATERIAL

- Polyamide 6.6

CERTIFICATIONS

- AH2 Rated
- 50 & 120LB Series UL Type 21S
- Flammability rating UL 94-V2



PART #	TENSILE STRENGTH (LBS.)	LENGTH	WIDTH	THICKNESS	MAX. BUNDLE DIAMETER	BAG QTY.	CASE QTY.	WEIGHT/CASE (LBS.)
BR4M9-C	18	4.1"	0.096"	0.035"	0.75"	100	1,000	1
BR6M9-C	18	6.1"	0.096"	0.05"	1.25"	100	1,000	1.1
BR8M9-C	18	8.1"	0.096"	0.05"	2.0"	100	1,000	1.5
BR5I9-C	40	5.7"	0.142"	0.05"	1.25"	100	1,000	2
BR8I9-C	40	8.7"	0.142"	0.05"	2.0"	100	1,000	2
BR7S9-C	50	7.6"	0.18"	0.054"	2.0"	100	1,000	2
BR11S9-C	50	11.1"	0.18"	0.054"	3.0"	100	1,000	3
BR14S9-C	50	14.6"	0.18"	0.054"	4.0"	100	1,000	3
BR8L9-C	120	9"	0.298"	0.069"	2.0"	100	1,000	2
BR11L9-C	120	12"	0.298"	0.069"	3.0"	100	1,000	2
BR14L9-C	120	14.6"	0.298"	0.069"	4.0"	100	1,000	3

Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.

Job Name/Title: _____

Model #: _____

Contractor: _____



Southwire™

CABLE TIES

NATURAL WHITE - INDOOR USE



PART #	TENSILE STRENGTH (LBS.)	LENGTH	WIDTH	THICKNESS	MAX. BUNDLE DIAMETER	BAG QTY.	CASE QTY.	WEIGHT/ CASE (LBS.)
BL4M9-C	18	4.1"	0.096"	0.035"	0.75"	100	10,000	6.8
BL4M9-M	18	4.1"	0.096"	0.035"	0.75"	1,000	10,000	6.8
BL6M9-C	18	6.1"	0.096"	0.05"	1.25"	100	20,000	24
BL6M9-M	18	6.1"	0.096"	0.05"	1.25"	1,000	20,000	24
BL8M9-C	18	8.1"	0.096"	0.05"	2.0"	100	20,000	30
BL8M9-M	18	8.1"	0.096"	0.05"	2.0"	1,000	20,000	30
BL5I9-C	40	5.7"	0.142"	0.05"	1.25"	100	10,000	17
BL5I9-M	40	5.7"	0.142"	0.05"	1.25"	1,000	10,000	17
BL8I9-C	40	8.7"	0.142"	0.05"	2.0"	100	10,000	24
BL8I9-M	40	8.7"	0.142"	0.05"	2.0"	1,000	10,000	24
BL7S9-C	50	7.6"	0.18"	0.054"	2.0"	100	10,000	30
BL7S9-M	50	7.6"	0.18"	0.054"	2.0"	1,000	10,000	30
BL11S9-C	50	11.1"	0.18"	0.054"	3.0"	100	5,000	20
BL11S9-D	50	11.1"	0.18"	0.054"	3.0"	500	5,000	20
BL11S9-M	50	11.1"	0.18"	0.054"	3.0"	1,000	5,000	20
BL14S9-C	50	14.6"	0.18"	0.054"	4.0"	100	5,000	25
BL14S9-D	50	14.6"	0.18"	0.054"	4.0"	500	5,000	25
BL14S9-M	50	14.6"	0.18"	0.054"	4.0"	1,000	5,000	25
BL8L9-C	120	9"	0.298"	0.069"	2.0"	100	2,500	21
BL8L9-D	120	9"	0.298"	0.069"	2.0"	500	2,500	21
BL11L9-C	120	12"	0.298"	0.069"	3.0"	100	2,000	22
BL11L9-D	120	12"	0.298"	0.069"	3.0"	500	2,000	22
BL14L9-C	120	14.6"	0.298"	0.069"	4.0"	100	2,000	26
BL24H9-L	175	24.1"	0.350"	0.087"	7.2"	50	500	15
BL30H9-L	175	29.6"	0.350"	0.087"	12.0"	50	500	19
BL36H9-L	175	36"	0.350"	0.087"	11.0"	50	500	21.5
BL48H9-L	175	48"	0.350"	0.087"	15.0"	50	500	27

Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.