

MAX JAX*

The Sumner* MAX JAX* fabrication stands are the ideal 5-legged stand for fit-up, rotating and welding.



- Designed for loads up to 4,500 lbs.
- Designed to hold 4" to 36" pipe depending on the head attachment
- 5-leg base construction with either a fixed base or adjustable 8" casters ensure stability
- Optional head attachments available



781403
MAX JAX* Kit



781460
MAX JAX* Basic

MAX JAX* PRODUCT DETAILS	
	Roll pipe through fab shop and save crane time (shown with recommended hold down device)
	PN 781050 Hold Down Device is a recommended safety option to retain pipe on stand

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM OPERATING HEIGHT	MINIMUM OPERATING HEIGHT	PIPE CAPACITY	LOAD CAPACITY	BASE WIDTH
781460	MAX JAX* Basic - includes vee head & leveling pads	MJAXB	661165814606	30"	2.5"	6" to 36"	4,500 lbs.	31"
781403	MAX JAX* Kit No. 1 - includes roller head kit & casters	MJAXKIT1	661165814033	38"	6"	4" to 36"	4,500 lbs.	31"

MAX JAX* OPTIONS

ITEM #	DESCRIPTION	MODEL #	UPC	WEIGHT CAPACITY(LBS.)
781381	Large Aluminum Roller Wheels (4)	781381	661165813814	4500
781382	Stainless Steel Sleeves (4)	781382	661165813821	4500
781383	Ball Transfers (2)	781383	661165813838	1000
781394	Rubber Wheel Kit (4)	781394	661165813944	1000
781397	Stainless Steel Ball Transfers (2)	781397	661165813975	1000
781406	Roller Head Kit (4 wheels)	781406	661165814064	4500
781407	Stainless Steel Roller Head Kit (4 wheels)	781407	661165814071	2000
781464	Caster Kit (5) Standard	781464	661165814644	4500
781465	Caster Kit (5) Steel Casters	781465	661165814651	4500
781050	Hold Down Device	781050	661165810509	-
781056	Hold Down Device Chain Ext. Kit (12")	781056	661165810561	-



**Roller Wheel Caster Kit
(PN 781465)**



**Stainless Steel (781407) or
Aluminum (781406) Roller
Head Kit**



**Stainless Steel Sleeves
(PN 781382)**



**Rubber Wheel Kit
(PN 781394)**



**Ball Transfers
(PN 781383)**



**Hold Down Device
(PN 781050)**