

Job Name/Title: _____ Catalog Number _____
 Contractor: _____ Notes: _____

LED Mini-Reflectors

7 Watt GU10 Series

Features

- No Mercury
- Up to 90% Energy Savings
- Last up to 10x longer than incandescent
- Dims down to 10% total light output*

Specs

- 120V
- 40° Beam Spread
- 80 CRI
- 2" MOD
- 15,000 Average Rated Life
- -40°F Minimum Start Temperature

Applications

- Ideal for track lighting



Catalog Number	Order Code	UPC	CCT	ENERGY STAR	Wattage	Lumens	CBCP	M.O.L.	M.O.L. (Inc Pins)	Equiv. Wattage	Case Qty
LGU10/7/830/D/G7	79421	751338030763	3000K	Y	6.5W	500	813	1.9"	2.15"	60W	1/10/100
LGU10/7/840/D/G7	79422	751338030787	4000K	Y	6.5W	500	833	1.9"	2.15"	60W	1/10/100
LGU10/7/850/D/G7	79423	751338030817	5000K	Y	6.5W	500	845	1.9"	2.15"	60W	1/10/100

Not for sale in California.

Specifications are subject to change without prior notice.

Suitable for use in enclosed fixtures

*Compatible with most leading edge or LED dimmers. Visit www.topaz-usa.com for up-to-date dimmer compatibility information.

