

REEL MAC™ JACKS

Sumner* brings you the best built, best value reel jack you can buy. Reel Mac™ jacks are available in three styles. Style numbers 60 and 70 feature screw-type adjustment with large 1-1/2" screws and large, easy to use handles. Style number 80 features a heavy duty ratchet handle.

FEATURES

- All steel construction
- Powder coat finish for superior durability and corrosion resistance
- Dependable Sumner* quality

NO. 60 (#780941)

Screw-type telescoping reel jack for 26" to 56" diameter reels

NO. 70 (#780942)

Screw-type telescoping reel jack for 46" to 96" diameter reels

NO. 80 (#780943)

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use



ACCESSORIES

Sumner* Reel Mac™ Spindles are designed to be used with Sumner* Reel Mac™ Jacks.

PART #	DESCRIPTION	HEIGHT RANGE	LOAD CAPACITY	USE WITH SPINDLE	WEIGHT
780941	Reel Mac No. 60	13" - 27" (33 - 68 cm)	2,500 lbs (1,135 kg)	61	30 lbs (13.6 kg)
780942	Reel Mac No. 70	21" - 54" (53 - 137 cm)	2,500 lbs (1,135 kg)	71	51 lbs (23.1 kg)
780943	Reel Mac No. 80	28" - 45" (71 - 114 cm)	3,700 lbs (1,700 kg)	81	105 lbs (47.6 kg)

PART #	SPINDLE #	DIAMETER	LOAD CAPACITY	USE WITH REEL MAC	WEIGHT
780229	61	2-3/8" (6.0 cm)	5,000 lbs (2,270 kg)	60	37 lbs (16.8 kg)
780230	71	2-3/8" (6.0 cm)	5,000 lbs (2,270 kg)	70	47 lbs (21.3 kg)
780231	81	3-1/2" (8.9 cm)	7,500 lbs (3,400 kg)	80	118 lbs (53.5 kg)