



DRAWING DIMENSIONS (LR)

LOCATION IN DRAWING	SIZE IN MM/INCH											
	½' (MLR50)		¾' (MLR75)		1' (MLR100)		1 ¼' (MLR125)		1 ½' (MLR150)		2' (MLR200)	
	MM	INCH	MM	INCH	MM	INCH	MM	INCH	MM	INCH	MM	INCH
A	118.60	4.67	137.100	5.40	157.500	6.20	205.00	8.07	206.00	8.11	268.00	10.55
B	34.900	1.37	41.000	1.61	47.150	1.86	64.150	2.53	67.200	2.65	81.15	3.19
C	56.140	2.21	59.7	2.35	71.300	2.81	90.100	3.55	90.720	3.57	107.00	4.21
D	79.150	3.12	94.900	3.74	111.250	4.38	152.170	5.99	153.400	6.04	204.00	8.03
E	37.700	1.48	40.500	1.59	50.00	1.97	68.00	2.68	71.00	2.80	89.000	3.50
F	26.500	1.04	33.000	1.30	37.965	1.49	54.500	2.15	57.200	2.25	68.65	2.70
G	99.00	3.90	117.200	4.61	136.200	5.19	182.900	7.20	183.00	7.20	240.00	9.45
H	33.600	1.32	36.500	1.44	45.500	1.79	63.500	2.50	66.00	2.60	84.50	3.33
I	89.15	3.155	94.42	3.717	109.1	4.295	151.66	5.970	147.65	5.813	196.58	7.740
J	28.50	1.122	35.35	1.391	42.20	1.661	49.05	1.931	55.90	2.200	69.60	2.740