



Southwire™

4-11/16" SQUARE SWIVEL FIXTURE HANGERS

20° MAX SWING FROM VERTICAL

FEATURES

- Keyhole slots allow for fast installation
- SC-507511BHF features hinged door design that allows the installer to mount the cover on box and hang fixtures in one easy step
- Wire termination can be completed with the door open reducing time and labor expenses

APPLICATIONS

- 4-11/16" square swivel fixture hangers are used to hang industrial lighting fixtures, security cameras, motion detectors, occupancy sensors and other electrical/electronic devices from overhead ceiling installations
- Perfect for industrial applications where the pipe stem or fixture might be subjected to motion or vibration

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL, cULus Listed



SC-507511B



SC-507511BHF

PART #	DESCRIPTION	CONDUIT SIZE	MASTER QTY.
SC-507511BHF	HANDS-FREE WIRING OF FIXTURE	1/2" OR 3/4"	10
SC-507511B	STANDARD TYPE	1/2" OR 3/4"	10

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.