



Southwire®

10035K

ELECTRICAL TEST KIT

Combines the 3 most commonly used electrical testers in one convenient kit.
Ideal for household repairs and electrical troubleshooting.

10030S MANUAL RANGING MULTIMETER

Easy to read backlit display with double molded housing and includes battery testing function



40010S RECEPTACLE TESTER

Checks for miswired outlets



40110N NON-CONTACT VOLTAGE DETECTOR

Check for live voltages.
100 - 1000V AC with built in flashlight.



7 FUNCTIONS

- AC Voltage
- DC Voltage
- DC Current
- Resistance
- Battery Test
- Continuity
- Diode Test



Southwire™

TOOLS & EQUIPMENT

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

1-855-SWTOOLS
(855-798-6657)



Southwiretools.com



Features

- 10030S Manual Ranging Multimeter with test leads
- 40110N Non-Contact AC Voltage Detector
- 40010S Receptacle Tester
- One 9 volt and two AAA batteries



Backlit display

Specifications

MANUAL RANGING MULTIMETER (10030S)

	RANGE	MAX. RESOLUTION	MAX. ACCURACY (% OF READING)
AC VOLTAGE	600V	0.1V	±1.2%
DC VOLTAGE	600V	0.1mV	±0.5%
DC CURRENT	10A	1µA	±1.0%
RESISTANCE	2000kΩ	0.1Ω	±0.8%
BATTERY TEST	1.5V, 9V	10mV	±1.0%
CONTINUITY	Audible threshold: Approximately 30Ω		
DIODE TEST	Yes		
DIMENSIONS	5.44 x 2.60 x 1.5 in. (138 x 64 x 38mm)		
WEIGHT	0.56 lbs (255g)		

NON-CONTACT AC VOLTAGE DETECTOR (40110N)

VOLTAGE DETECTION RATE	100V AC to 1000V AC
FREQUENCY RANGE	50/60Hz
DIMENSIONS	6.23 x 0.83 x 0.99 in.
WEIGHT	3.7oz (105g)

RECEPTACLE TESTER (40010S)

HEIGHT	3.43 in. (87mm)
WIDTH	1.73 in. (44mm)
DEPTH	0.95 in. (24mm)

