

Weld Gas Analyzer

SUMNER

Sumner Manufacturing Co., Inc.



Argo-Naught Weld Gas Analyzer:

- ✓ Hermetically sealed, robust housing
- ✓ Air and water-tight
- ✓ State of the art electronics
- ✓ High measurement accuracy
- ✓ Quick response time
- ✓ Clear, large display
- ✓ Increased sensor life expectancy



The Argo-Naught Weld Gas Analyzer accurately monitors oxygen levels while using inert gas to purge stainless steel, titanium and other reactive metal. The Argo-Naught Weld Gas Analyzer measures oxygen content in the weld chamber down to 0.1% (1000 ppm), helps save on argon gas consumption and increases the welder's production rate.



779281 Argo-Naught Weld Gas Analyzer Kit

Part No.	Description	Weight	
		lb	kg
779281	Argo-Naught Weld Gas Analyzer Kit – Includes case, Argo-Naught Analyzer, 2 AA batteries, 6-1/2 foot (2 m) rubber hose, stainless steel probe, rubber vacuum bulb	1.3	0.6

SUMNER

Sumner Manufacturing Co., Inc.

www.sumner.com

DISTRIBUTED BY:

Sumner - U.S. 7514 Alabonson Road • Houston, TX 77088 • Ph: 281-999-6900 • Fax: 281-999-6966

Sumner - Canada 75 Saltsman Drive, Unit 5 • Cambridge, Ontario N3H 4R7 • Ph: 519-653-5300 • Fax: 519-653-5305

Sumner - Netherlands Midden Engweg 21 • NL-3882TS Putten • The Netherlands • Ph: +31 (0) 85 489 0284 • europesales@sumner.com

Sumner - U.K. Unit 3 Kempton Road • Keytec 7 Business Park • Pershore, Worcestershire WR10 2TA • Ph: (44) 01386 556278 • Fax: (44) 01386 556776