

LED COMMERCIAL DOWNLIGHTS CANLESS RECESSED WITH POWER & CCT SELECT

SUGGESTED APPLICATIONS

- · Commercial (Offices, conference rooms and hallways)
- · Multi-family buildings (interior, bathrooms and exterior)
- Hospitality (Hotel lobbies, collaborative spaces and restaurants)
- Retail, Education, Hospitals and Airports

FEATURES

- Power & CCT field selectable switch to adjust between 3 wattages and 5 color temperatures
- Canless design no housing needed for easy installation
- Available with Integrated or Remote Drivers in 4", 6", 8" and 10" sizes
- Deep regress design provides low glare and comfortable optical distribution
- Spring clips and quick-connects allow for hassle free installation

• Emergency battery backup option with remote mounted test switch

Suitable for insulated and non-insulated applications





INPUT VOLTAGE: 120-277V

FREQUENCY: 50-60HZ

POWER FACTOR, THD %:

>0.9/20%

DIMMABLE: 0-10V, DOWN TO 10%

EFFICACY: UP TO 85 LPW

MINIMUM CRI: 90

LIFETIME (L70): 50,000 HOURS

AMBIENT OPERATING

TEMPERATURE: -13°F TO 104°F

SUITABLE FOR CLOSET APPLICATIONS: NO

























Job Name/Title:	Model #:	Fixture Type:



LED COMMERCIAL DOWNLIGHTS CANLESS RECESSED WITH POWER & CCT SELECT





ITEM SPECIFICATIONS | ORDER INFO

EM SPECIFICATIONS ORDER INFO											
MODEL #	ORDER CODE	UPC	SIZE (TRADE)	INPUT VOLTAGE MAX. INPUT CURRENT	POWER SELCTABLE WATTAGE	LUMENS @2700K		LUMENS @3500K			BEAM ANGLE
						600	600	600	630	630	
CDL4S-13WPCS-U	75865	032886314186	4"	120-277V 120mA	9W	850	850	850	900	900	90°
					13W	1,150	1,150	1,150	1,200	1,200	
					8W	750	750	750	800	800	95°
CDL6S-16WPCS-U	75866	032886314193	6"	120-277V 150mA	12W	1,100	1,100	1,100	1,150	1,150	
					16W	1,450	1,450	1,450	1,500	1,500	
					15W	1,500	1,500	1,550	1,550	1,550	
CDL8S-26WPCS-U 75867 032886314056	8"	120-277V 240mA	20W	1,950	1,950	1,950	2,000	2,000	95°		
				2101111	26W	2,450	2,450	2,450	2,500	2,500	
			20W	1,950	1,950	1,950	2,000	2,000			
CDL10S-36WPCS-U 75868 03288	032886314063	10"	120-277V 340mA	25W	2,450	2,450	2,450	2,500	2,500	100°	
			2.2	36W	3,350	3,350	3,350	3,500	3,500		
WITH REMOTE DRIVER											
				6W	600	600	600	630	630		
CDL4S-RM-12WPCS-U 75869 032886314	032886314070	4"	120-277V 110mA	9W	850	850	850	900	900	95°	
					12W	1,050	1,050	1,050	1,100	1,100	
					12W	1,100	1,100	1,100	1,100	1,100	
CDL6S-RM-24WPCS-U 75870 0328863140	032886314087	6"	120-277V 220mA	16W	1,500	1,500	1,500	1,500	1,500	95°	
				24W	1,950	1,950	1,950	2,000	2,000		
			16W	1,450	1,450	1,450	1,500	1,500			
CDL8S-RM-30WPCS-U	75871	032886314094	8"	120-277V 280mA	22W	1,950	1,950	1,950	2,000	2,000	95°
					30W	2,450	2,450	2,500	2,500	2,600	

ORDERING GUIDE

Example: CDL6S-RM-24WPCS-U

PRODUCT	SIZE	TRIM STYLE	DRIVER TYPE	POWER SELECTABLE	OPTIONS	
	4"	S = SMOOTH		13WPCS = 6 9 13W		
	6"		Blank= integrated driver	16WPCS = 8 12 16W		
CDL = COMMERCIAL DOWNLIGHTS 1	8"			26WPCS = 15 20 26W		
	10"			36WPCS = 20l25l36W	U = UNIVERSAL INPUT VOLTAGE 120-277V	
	4"			12WPCS = 6 9 12W	.20 2///	
	6"		RM = REMOTE DRIVER	24WPCS = 12 16 24W		
	8"			30WPCS = 16 22 30W		






LED COMMERCIAL DOWNLIGHTS CANLESS RECESSED WITH POWER & CCT SELECT





DIMENSIONS | WEIGHT

MODEL #	INCANDESCENT REPLACEMENT	A (IN)	B (IN)	C (IN)	WEIGHT (LBS)	PALLET QUANTITY (PCS)* 48" X 40" X 60"
CDL4S-13WPCS-U	40W/60W/75W	5.98	4.53	4.21	1.34	144
CDL6S-16WPCS-U	60W/75W/100W	8.41	5.87	4.84	1.76	96
CDL8S-26WPCS-U	100W/125W/150W	10.04	7.32	5.17	1.92	72
CDL10S-36WPCS-U	125W/150W/200W	11.38	8.63	5.64	2.27	48
CDL4S-RM-12WPCS-U	40W/60W/75W	5.04	3.89	1.98	0.76	270
CDL6S-RM-24WPCS-U	75W/100W/125W	7.36	4.31	2.85	0.91	144
CDL8S-RM-30WPCS-U	100W/126W/150W	8.66	6.41	3.39	1.05	96



NOTES

Dimming with standard 0-10V control system or wall dimmers. Dimming complies with IEC60929 Annex E. Fixture may not be compatible with all dimmers. Dimming performance may vary based on selected dimmer. Contact your local Southwire representative for a list of compatible dimmers.

Power & CCT selectable models: default settings are 4000K at the highest wattage.

FIVE (5) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC: For details visit: https://southwire.com/resources/warranties.
This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. CAN-ICES-003B/NMB-003B

Specifications are subject to change without prior notice. Replacement wattage shown depends on application and fixture.

^{*} Pallet quantities may vary



LED COMMERCIAL DOWNLIGHTS ACCESSORIES (SOLD SEPARATELY)



EMERGENCY BATTERY BACKUP WITH REMOTE TEST SWITCH

This inline EMBB is for use with all Topaz Commercial Canless Downlights with Internal or Remote Drivers. Can also be used for most Topaz lighting platforms (email Lighting@Southwire.com for details).

- 8W EMBB
- Provides 90-minute duration
- 120-277V input
- Battery capacity is greater than 60% from factory
- 12-month shelf life

Note: Be sure to follow your local fire and safety regulations regarding testing.



GOOF RINGS

This overlay solution is ideal for hiding oversized or miscut ceiling holes.

 SIMPLE INSTALL - The overlay easily slips between the ceiling and the commercial downlight trims. There is also at least one small nail hole in the goof ring to allow more permanent mounting.



CDL-DWP





NEW CONSTRUCTION PAN AND ACCESSORIES

- CDL-DWP (New Construction/Drywall Pan): recommended for drywall ceilings and suspended drop ceilings. Designed to fit between standard joists from 12 to 24 inches; also fits standard bar channels in grid drop ceilings. The universal pan fits 3, 4, 6, 8 and 10-inch canless downlight fixtures.
- CDL-HB (Hanger Bars): recommended for new construction projects where joists are present. Extend from 12 to 24 inches. Hanger Bars are required for T-grid ceilings as they provide support for the tile by removing the weight of the fixture. Extend the Hanger Bars and secure to the channel bars.
- CDL-J-BOX (Junction Box): recommended for integrated driver fixtures only (remote driver fixtures include j-box). Once assembled, the j-box attaches to the top of frame pan using metal tabs.

COLOR TRIM FINISHES

These smooth high-quality aluminum trims easily attach to the downlights by bending the metal tabs around the edges of the trims. Note: only compatible with the integrated driver fixtures.



BRUSHED NICKLE SMOOTH (BN-S)



MATTE BLACK SMOOTH (MB-S)



BRONZE SMOOTH (BZ-S)



MATTE SILVER SMOOTH (MS-S)



LED COMMERCIAL DOWNLIGHTS ACCESSORIES (SOLD SEPARATELY)

ACCESSORIES (SOLD SEPARATELY)

MODEL #	ORDER CODE	DESCRIPTION
CDL-EMBB8	75876	8W EMERGENCY BATTERY BACKUP DRIVER
		GOOF RINGS
CDL-GR4	75872	4" GOOF RING
CDL-GR6	75873	6" GOOF RING
CDL-GR8	75874	8" GOOF RING
CDL-GR10	75875	10" GOOF RING
		MOUNTING
CDL-DWP	75877	DRY WALL PAN
CDL-HB	75878	HANGER BARS
CDL-J-BOX	75879	J-BOX
		COLOR TRIMS
CDL4-TRIM-MB-S	76922	4" MATTE BLACK SMOOTH TRIM
CDL4-TRIM-BN-S	76923	4" BRUSHED NICKLE SMOOTH TRIM
CDL4-TRIM-BZ-S	76924	4" BRONZE SMOOTH TRIM
CDL4-TRIM-MS-S	76925	4" MATTE SILVER SMOOTH TRIM
CDL6-TRIM-MB-S	76926	6" MATTE BLACK SMOOTH TRIM
CDL6-TRIM-BN-S	76927	6" BRUSHED NICKLE SMOOTH TRIM
CDL6-TRIM-BZ-S	76928	6" BRONZE SMOOTH TRIM
CDL6-TRIM-MS-S	76929	6" MATTE SILVER SMOOTH TRIM
CDL8-TRIM-MB-S	76930	8" MATTE BLACK SMOOTH TRIM
CDL8-TRIM-BN-S	76931	8" BRUSHED NICKLE SMOOTH TRIM
CDL8-TRIM-BZ-S	76932	8" BRONZE SMOOTH TRIM
CDL8-TRIM-MS-S	76933	8" MATTE SILVER SMOOTH TRIM
CDL10-TRIM-MB-S	76934	10" MATTE BLACK SMOOTH TRIM
CDL10-TRIM-BN-S	76935	10" BRUSHED NICKLE SMOOTH TRIM
CDL10-TRIM-BZ-S	76936	10" BRONZE SMOOTH SMOOTH TRIM
CDL10-TRIM-MS-S	76937	10" MATTE SILVER SMOOTH TRIM

