

LED Lamps

ANTIQUE / FILAMENT STYLE



Replicates the Traditional Vintage Look and Feel of Incandescent Bulbs

Topaz Antique/Filament Style LED Lamps replicate the traditional vintage look and feel of incandescent bulbs while providing significant energy savings and a 15,000 hour lifetime. These lamps are designed to produce an elegant ambient effect and are perfect for hospitality, restaurant, residential and retail applications. The line is offered in S19, A19, A23, Globe and candelabra styles and are dimmable for additional ambiance or mood lighting control.

FEATURES

- Up to 90% energy savings compared to incandescent lamps
- Advanced optics and thermal construction
- Dimmable down to 10% of total light output
- RoHS compliant and mercury free
- A19, A23, G30 and S19 lamps have amber glass finish

SUGGESTED APPLICATIONS

- Decorative lighting, wall sconces, chandeliers
- Residential, hospitality, commercial





Job Name/Title: _____ Catalog Number _____

Contractor: _____ Notes: _____

LED Lamps FILAMENT STYLE

GENERAL SPECIFICATIONS

Input Voltage: 120V

THD: <15%

Ambient Temperature: -4°F to 104°F



SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Wattage	Input Voltage	Shape	Base	CRI	CCT	Lumens	LPW	Avg. Rated Life	MOL	Replacement Wattage	Dimming	PK QTY
Medium Base Filament Style															
LA19/7/822/ANTQ-61	79305	751338023673	7W	120	A19	E26	80	2200K	650	93	15,000	4.05"	60	Y	1/10/60
LA23/5/822/ANTQ-83	79238	751338001626	5W	120	A23	E26	80	2200K	400	80	15,000	5.25"	40	Y	1/6/24
LG30/5/822/ANTQ-83	79245	751338001701	5W	120	G30	E26	80	2200K	400	80	15,000	5.38"	40	Y	1/6/24
LS19/5/822/ANTQ-61	79308	751338023680	5.5W	120	S19	E26	80	2200K	400	73	15,000	5.5"	40	Y	1/10/60
Candelabra Base Filament Style															
LCFC/5/827/ANTQ-61	79306	751338023697	5.5W	120	C11	E12	80	2700	500	91	15,000	4.15"	60	Y	1/10/100
LCTC/5/827/ANTQ-61	79307	751338023710	5.5W	120	B11	E12	80	2700	500	91	15,000	3.75"	60	Y	1/10/100

Not for sale in California.

NOMENCLATURE

Example: LA19/7/822/ANTQ

LA19 = LED A19 Shape / 7 = 7 Watt / 822 = 2200K / ANTQ = Antique

ENERGY SAVINGS

Item #	LED Wattage	Incandescent Wattage	Energy Savings, Watts	Yearly Cost Savings	5 Year Cost Savings
Based on 8 hours/day and \$0.11¢/kWh					
LA19/7/822/ANTQ-61	7W	60W	53W	\$17.02	\$85.10
LA23/5/822/ANTQ-83	5W	40W	35W	\$11.24	\$56.20
LG30/5/822/ANTQ-83	5W	40W	35W	\$11.24	\$56.20
LS19/5/822/ANTQ-61	5.5W	40W	34.5W	\$11.08	\$55.40
LCFC/5/827/ANTQ-61	5.5W	60W	54.5W	\$17.51	\$87.55
LCTC/5/827/ANTQ-61	5.5W	60W	54.5W	\$17.51	\$87.55

NOTES:

*Dimming - These lamps are designed to be compatible with most leading edge or LED type dimmers. (Dimming range 100% - 10%) Performance may vary depending on dimmer.

This device is not intended for use with emergency exits.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

THREE (3) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED lamps shall be free from defects of material and workmanship for a period of three (3) years from the date of purchase. Based on 12 hours of use per day, TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice.

Revised July 2020