



Southwire™

FLEXIBLE LIQUIDTIGHT CONDUIT

METALLIC - COIL

FEATURES

- Crush and corrosion resistant steel core for lasting mechanical protection
- EF PVC jacket is oil and sunlight resistant
- Smooth interior for easy wire pull through

APPLICATION

- For use in damp or wet locations, suitable for commercial and industrial use
- Non UL

STANDARD MATERIAL

- EF PVC jacketed steel core coil wrapped in clear plastic shrink wrap



6101

PART #	SIZE	FEET COIL	MASTER QTY.	WEIGHT/ CASE (LBS.)	INSIDE DIAMETER		OUTSIDE DIAMETER	
					MIN.	MAX.	MIN.	MAX.
6100	3/8"	100'	100'	16	.484"	.504"	.689"	.709"
6101	1/2"	100'	100'	26	.622"	.642"	.819"	.839"
6102	3/4"	100'	100'	31	.815"	.835"	1.032"	1.051"
6103	1"	100'	100'	44	1.032"	1.055"	1.287"	1.315"
6104	1-1/4"	50'	50'	46	1.37"	1.394"	1.63"	1.661"
6105	1-1/2"	50'	50'	35	1.579"	1.598"	1.866"	1.902"
6106	2"	25'	25'	22	2.02"	2.043"	2.339"	2.374"
6106C50	2"	50'	50'	49	2.02"	2.043"	2.339"	2.374"
6107	2-1/2"	25'	25'	42	2.48"	2.504"	2.839"	2.874"
6108	3"	25'	25'	53	3.071"	3.102"	3.461"	3.50"
6109	3-1/2"	25'	25'	55	3.50"	3.54"	3.96"	4"
6110	4"	25'	25'	57	4"	4.039"	4.457"	4.50"

Rev. 0, 01/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.