



LED String Light FAQ'S

What are the advantages of switching to LED String Lights?

Long life, maintenance-free, and energy savings to name a few. The Southwire LED String Lights are the perfect temporary jobsite lights for any construction or jobsite!

Do the LED String Lights require any bulb/lamp replacement?

No, since LED String Lights are an integral fixture with no bulbs, they require no maintenance. The LED String Light is designed for a maintenance-free long-life.

Is the LED String Light outdoor rated?

Yes, the LED String Light is IP65 Rated, and protected from the ingress of dust and water.

What is the expected life of an LED String Light?

50,000 Hours at 70% Lumen Output.

Can the LED String Light be dimmed?

No, the LED String Light cannot be dimmed, similar to the existing 400W MH Fixture.

Are the LED String Lights compatible with 277V?

No, the plug in LED String Light can only be used with 120Vac Input.

Can the LED String Lights be daisy-chained?

Yes, you can daisy-chain up to 8 strings for the 100' version and 20 strings for the 50' version.

