



Southwire™

TOP-FLEX II TUBING

NON-METALLIC - BLACK

FEATURES

- Resists corrosion, abrasion, oil, water, acid, metal shavings, and rough environments

APPLICATION

- Indoor or outdoor use

STANDARD MATERIAL

- Integral Rigid and flexible PVC construction



HF214



PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)	OUTSIDE DIAMETER		INSIDE DIAMETER		WALL THICKNESS
				MIN.	MAX.	MIN.	MAX.	
HF214	1/4"	100'	4	.56"	.575"	.385"	.405"	.17"
HF238	3/8"	100'	6	.69"	.71"	.484"	.504"	.21"
HF212	1/2"	100'	8	.82"	.84"	.622"	.642"	.21"
HF234	3/4"	100'	10	1.03"	1.05"	.82"	.84"	.21"
HF21	1"	100'	15	1.29"	1.315"	1.041"	1.066"	.25"
HF2114	1-1/4"	100'	19	1.63"	1.66"	1.38"	1.41"	.25"
HF2112	1-1/2"	50'	22	1.865"	1.90"	1.575"	1.60"	.30"
HF22	2"	50'	60	2.34"	2.375"	2.02"	2.045"	.33"

Rev. 0, 01/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.