



Southwire™

TOOLS & EQUIPMENT

RR-SW30, 30K REEL ROLLER

Southwire now offers the RR-SW30. With its heavy duty, all welded construction it is built to handle 30,000lbs. With convenient fork tubes and lifting eyes, maneuvering the equipment around the jobsite is easy. You can now safely operate the reel roller by standing outside of the wires path by remotely operating the unit with the foot control and the variable speed adjustment. When the job is finished and it's time to store the unit, the RR-SW30 will not take up as much room as traditional reel rollers with our new stackability feature. All that is needed is a 2" piece of rigid conduit cut to the desired length and installed in the feature. This unit can be stacked 4 units high.

**HANDLES UP TO
30,000 LBS REELS**

STACKABLE TO 4 UNITS HIGH

SPEED CONTROL ADJUSTMENT

**FOOT CONTROL FOR
REMOTE OPERATION**

HEAVY DUTY 10-AMP MOTOR

**CONVIENENT FORK
TUBES ON BOTH SIDES**

MADE IN THE USA

**HEAVY DUTY ALL
WELDED CONTRUCTION**

3-4 WEEK LEAD TIME

10 YEAR LIFE OF ASSET



MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
RR-SW30	65241740	30k Reel Roller	23"	74"	122"	2,000 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.