



Southwire™

CABLE TIES

BLACK UV STABILIZED - INDOOR/OUTDOOR USE

FEATURES

- Operating temperature minimum -40°F to maximum 185°F
- Easy grab tip for pick up from flat surfaces
- Low insertion for quick installation
- UV Resistant
- High Yield Strength

APPLICATION

- Safely and easily secures wire bundles and harness components

STANDARD MATERIAL

- Polyamide 6.6 UV Resistant

CERTIFICATIONS

- AH2 Rated
- 50 & 120LB Series UL Type 21S
- Flammability rating UL 94-V2



| PART # | TENSILE STRENGTH (LBS.) | LENGTH | WIDTH | THICKNESS | MAX. BUNDLE DIAMETER | BAG QTY. | CASE QTY. | WEIGHT/CASE (LBS.) |
|----------|-------------------------|--------|--------|-----------|----------------------|----------|-----------|--------------------|
| BR4M0-C | 18 | 4.1" | 0.096" | 0.035" | 0.75" | 100 | 1,000 | 1 |
| BR6M0-C | 18 | 6.1" | 0.096" | 0.05" | 1.25" | 100 | 1,000 | 1.1 |
| BR8M0-C | 18 | 8.1" | 0.096" | 0.05" | 2.0" | 100 | 1,000 | 1.5 |
| BR5I0-C | 40 | 5.7" | 0.142" | 0.05" | 1.25" | 100 | 1,000 | 2 |
| BR8I0-C | 40 | 8.7" | 0.142" | 0.05" | 2.0" | 100 | 1,000 | 2 |
| BR7S0-C | 50 | 7.6" | 0.18" | 0.054" | 2.0" | 100 | 1,000 | 2 |
| BR11S0-C | 50 | 11.1" | 0.18" | 0.054" | 3.0" | 100 | 1,000 | 3 |
| BR14S0-C | 50 | 14.6" | 0.18" | 0.054" | 4.0" | 100 | 1,000 | 3 |
| BR8L0-C | 120 | 9" | 0.298" | 0.069" | 2.0" | 100 | 1,000 | 2 |
| BR11L0-C | 120 | 12" | 0.298" | 0.069" | 3.0" | 100 | 1,000 | 2 |
| BR14L0-C | 120 | 14.6" | 0.298" | 0.069" | 4.0" | 100 | 1,000 | 3 |

Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.

Job Name/Title: _____

Model #: _____

Contractor: _____



Southwire™

CABLE TIES

BLACK UV STABILIZED - INDOOR/OUTDOOR USE



| PART # | TENSILE STRENGTH (LBS.) | LENGTH | WIDTH | THICKNESS | MAX. BUNDLE DIAMETER | BAG QTY. | CASE QTY. | WEIGHT/CASE (LBS.) |
|----------|-------------------------|--------|--------|-----------|----------------------|----------|-----------|--------------------|
| BL4M0-C | 18 | 4.1" | 0.096" | 0.035" | 0.75" | 100 | 10,000 | 6.8 |
| BL4M0-M | 18 | 4.1" | 0.096" | 0.035" | 0.75" | 1,000 | 10,000 | 6.8 |
| BL6M0-C | 18 | 6.1" | 0.096" | 0.05" | 1.25" | 100 | 20,000 | 24 |
| BL6M0-M | 18 | 6.1" | 0.096" | 0.05" | 1.25" | 1,000 | 20,000 | 24 |
| BL8M0-C | 18 | 8.1" | 0.096" | 0.05" | 2.0" | 100 | 20,000 | 30 |
| BL8M0-M | 18 | 8.1" | 0.096" | 0.05" | 2.0" | 1,000 | 20,000 | 30 |
| BL5I0-C | 40 | 5.7" | 0.142" | 0.05" | 1.25" | 100 | 10,000 | 17 |
| BL5I0-M | 40 | 5.7" | 0.142" | 0.05" | 1.25" | 1,000 | 10,000 | 17 |
| BL8I0-C | 40 | 8.7" | 0.142" | 0.05" | 2.0" | 100 | 10,000 | 24 |
| BL8I0-M | 40 | 8.7" | 0.142" | 0.05" | 2.0" | 1,000 | 10,000 | 24 |
| BL7S0-C | 50 | 7.6" | 0.18" | 0.054" | 2.0" | 100 | 10,000 | 30 |
| BL7S0-M | 50 | 7.6" | 0.18" | 0.054" | 2.0" | 1,000 | 10,000 | 30 |
| BL11S0-C | 50 | 11.1" | 0.18" | 0.054" | 3.0" | 100 | 5,000 | 20 |
| BL11S0-D | 50 | 11.1" | 0.18" | 0.054" | 3.0" | 500 | 5,000 | 20 |
| BL11S0-M | 50 | 11.1" | 0.18" | 0.054" | 3.0" | 1,000 | 5,000 | 20 |
| BL14S0-C | 50 | 14.6" | 0.18" | 0.054" | 4.0" | 100 | 5,000 | 25 |
| BL14S0-D | 50 | 14.6" | 0.18" | 0.054" | 4.0" | 500 | 5,000 | 25 |
| BL14S0-M | 50 | 14.6" | 0.18" | 0.054" | 4.0" | 1,000 | 5,000 | 25 |
| BL8L0-C | 120 | 9" | 0.298" | 0.069" | 2.0" | 100 | 2,500 | 21 |
| BL8L0-D | 120 | 9" | 0.298" | 0.069" | 2.0" | 500 | 2,500 | 21 |
| BL11L0-C | 120 | 12" | 0.298" | 0.069" | 3.0" | 100 | 2,000 | 22 |
| BL11L0-D | 120 | 12" | 0.298" | 0.069" | 3.0" | 500 | 2,000 | 22 |
| BL14L0-C | 120 | 14.6" | 0.298" | 0.069" | 4.0" | 100 | 2,000 | 26 |
| BL24H0-L | 175 | 24.1" | 0.350" | 0.087" | 7.2" | 50 | 500 | 15 |
| BL30H0-L | 175 | 29.6" | 0.350" | 0.087" | 12.0" | 50 | 500 | 19 |
| BL36H0-L | 175 | 36" | 0.350" | 0.087" | 11.0" | 50 | 500 | 21.5 |
| BL48H0-L | 175 | 48" | 0.350" | 0.087" | 15.0" | 50 | 500 | 27 |

Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.