



Southwire™

SPLIT BOLT CONNECTORS

SOLDERLESS - FOR COPPER & COPPERWELD WIRE - COPPER ALLOY

FEATURES

- Features copper pressure bar and hex style head
- Highly resistant to corrosion and cracking
- Provides high contact pressure between conductors
- UL 467 suitable for direct burial

APPLICATIONS

- For copper to copper connections including copperweld wire

STANDARD MATERIAL

- Copper alloy



690



PART #	WIRE SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	MAXIMUM RUN TO MINIMUM TAP	
690	#10	100	1000	2	16 STR	10 STR
691TZ	#8	100	1000	3	8 STR 8 SOL	16 STR 16 SOL
692TZ	#6	100	1000	5	6 SOL	16 SOL
694	#4	50	500	8	4 STR 4 SOL	14 STR 14 SOL
695	#2	50	500	11	2 STR 2 SOL	14 STR 14 SOL
696	1/0	50	500	8	1/0 STR 1/0 SOL	14 STR 14 SOL
697	2/0	25	250	7	2/0 STR 2/0 SOL	14 STR 14 SOL
698TZ	3/0	25	25	8	3/0 STR 3/0 SOL	8 STR 8 SOL
699TZ	4/0 – 250 MCM	5	50	10	250 STR	8 STR
700TZ	350 MCM	---	6	5	350 STR	1/0 STR
701TZ	500 MCM	---	6	5	500 STR	2/0 STR
702TZ	750 MCM	---	3	5	350 MCM	750 MCM
703TZ	1000 MCM	---	4	10	500 MCM	1000 MCM

*UL listed for electrical power applications (not approved for grounding, bonding, and direct burial)

Rev. 0, 10/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.