



Southwire™

MOGUL CONDUIT BODIES WITH COVER AND GASKET

LL TYPE - HOT DIP GALVANIZED - MALLEABLE IRON

FEATURES

- c(UL)us wet locations
- Threaded NPT tapered hubs for Rigid and IMC conduit
- Smooth and round integral hub bushings protect conductor insulation
- Access to wiring for maintenance and future changes
- Assembled with raised cover, gasket and stainless steel cover screws

APPLICATION

- Use to pull straight or 90° angle turns or making taps and splices
- Provides long and large openings for pulling large conductors, splicing and taps
- Serve as a pull outlets for conductors that are stiff

STANDARD MATERIAL

- Body - Malleable iron
- Gasket - Neoprene rubber
- Screws - Stainless steel

STANDARD FINISH



- Hot dip galvanized

CERTIFICATIONS

- UL Standard: UL 514A - UL 514D
- Fed. Spec: W-C-586D, A-A-50563
- NEMA: FB 1-2014 - NEMA 3R



MLL3CGHDG



PART #	SIZE	WIRE SIZE MAX. NUMBER	WIRE SIZE MAX. SIZE	INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C	D	E
MLL3CGHDG	1"	3	4 AWG	19	1	4	8.62"	5.98"	1.71"	3.12"	1.87"
MLL4CGHDG	1-1/4"	3	2 AWG	25	1	6	8.62"	5.98"	1.71"	3.12"	2.31"
MLL5CGHDG	1-1/2"	3	1/0 AWG	57	1	10	12.72"	10"	2.26"	4.08"	2.58"
MLL6CGHDG	2"	3	4/0 AWG	75	1	14	12.72"	10"	2.26"	4.08"	3.17"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.