

## LED 3-Way Omnidirectional A19 and A21



A19

A21

### Adjustable Ambiance to Suit All of Your Needs

Topaz LED 3-Way Omnidirectional A19 and A21 lamps are ideal for both residential and commercial settings including down lights, wall sconces, ceiling fans, table and floor lamps. True omnidirectional light distribution - 300° beam spread. Regulate between focused task lighting, general lighting, and relaxed mood lighting.

### FEATURES

- 3 light levels (For use with 3-way light switch)
- 85% energy savings compared to 100W incandescent
- Suitable for use in totally enclosed luminaires
- Long life - up to 10X longer than traditional incandescents
- RoHS compliant and mercury free
- Plastic lens material provides shatter protection

### SUGGESTED APPLICATIONS

- Fan lights, decorative, recessed, task lighting
- Residential, hospitality, retail, restaurants, commercial



## LED 3-Way Omnidirectional A19 and A21

### GENERAL SPECIFICATIONS

**Input Voltage:** 120V  
**Average Rated Life:** 25,000 Hours  
**Base:** Medium E26d  
**CRI:** 80  
**THD:** <15%  
**Beam Angle:** 300°  
**Equivalent Wattage:** 30/70/100W  
**Ambient Operating Temp:** -4°F to 104°F



### SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Wattage	CCT	Initial Lumens	Lumens Per Watt	ENERGY STAR	PK-QTY
LA19/12/27K/3W*	78983	751338019027	3/9/12W	2700K	280/950/1200	93/105/100	Y	1/6/24
LA19/12/30K/3W*	78984	751338019034	3/9/12W	3000K	280/950/1200	93/105/100	Y	1/6/24
LA21/16/827/3W	78920	751338001756	3/11/16W	2700K	350/1200/1600	117/109/100	-	1/6/24
LA21/16/830/3W	78921	751338001763	3/11/16W	3000K	360/1240/1650	120/113/103	-	1/6/24

Not for sale in California.

### NOMENCLATURE

Example: LA19/12/27K/3W

LA19 = LED A19 Shape / 12 = 12 Watt / 27K = 2700K / 3W = 3-Way  
30K = 3000K

LA21 = LED A21 Shape / 16 = 16 Watt / 827 = 2700K / 3W = 3-Way  
830 = 3000K

### ENERGY SAVINGS

	LED Wattage	Incandescent Wattage	Energy Saving, Watts	Yearly Saving, Fixture	5 Year Cost Savings
<b>Based on 3 hours/day and \$0.11/kWh</b>					
LA19/12/XXK/D	12W	100W	88W	\$17.67	\$88.35
LA21/16/XXK/D	16W	100W	84W	\$16.86	\$84.30

#### NOTES:

\* Replaces LA21/16/8XX/3W. Check with sales for availability.  
Suitable for enclosed fixtures. This device is not intended for use with emergency exits.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

FIVE (5) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED lamps shall be free from defects of material and workmanship for a period of five (5) years from the date of purchase. Based on 12 hours of use per day. TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice.

Revised July 2020