

Steady arm G1" straight with eye and insulation 3 kV, adjustable, L = 1500 mm, with thread 5/8", SST

Item number D2421-05



Dimensions

A: 10.000 mm
Ø1: 23 mm
Ø3: 33.7 mm
Ø2: 5/8"
L: 1500 mm

Material and weight

Material: SST
Weight: 4.420 kg

Loads

Breaking load F: 5.5 kN

Specification

Operating voltage: max. 3000 V
Minimum creeping distance: 85 mm for insulator

Comments

- Steady arm G1" are also available in aluminum (with reduced breaking load and low weight)
- Minimum order quantity on request
- Other lengths on request



Southwire™



A COLAS RAIL COMPANY

Contact Us: Transit@southwire.com