

LED Small Flood Light SPEC SHEET



F-FL/13/50K/KN/BZ



F-FL/50/50K/TR/BZ



F-FL/30/50K/KN/BZ
F-FL/50/50K/KN/BZ

Uniform Illumination, Low Profile Housing Design, High Efficacy, Long Lifespan

These easy to install fixtures feature die cast housing with powder coat finish, stainless hardware and an impact resistant lens. DLC qualified and available in 13W, 30W or 50W. Wide light distribution, 7H x 6V optics make this a great choice for illuminating small signs and building facades, monuments, pedestrian pathways and landscaping. Mounting options include 1/2" knuckle or trunion with an optional photocell for additional energy savings.

FEATURES

- Die cast aluminum housing with integrated thermal management and impact resistant polycarbonate optical lens.
- Stainless steel hardware
- Up to 113 LPW
- Knuckle (1/2") or Trunion mounting options
- Dark bronze powder coat finish (other colors available by special order)
- DLC Qualified
- 5 year warranty
- Suitable for use with photocells

APPLICATIONS

- Pedestrian walkways, area of security, landscaping
- Building façades
- Signage, monuments





Job Name/Title: _____ Catalog Number _____

Contractor: _____ Notes: _____

LED Small Flood Light SPEC SHEET

GENERAL SPECIFICATIONS

- Voltage:** 120-277V 50/60Hz
- Power Factor:** >0.9
- THD:** <20%
- Average Rated Life:** 50,000 (L70)
- CRI:** 80
- CCT:** 5000K
- NEMA Distribution:** 7Hx6V
- Ambient Temp:** -40° to 104°F
- Surge Protection:** 4KV
- Effective Projected Area (EPA):** 0.12 ft² (13W), 0.38 ft² (30 and 50W)



13W Knuckle



50W Trunnion



**30W and 50W
Knuckle**

SPECIFICATIONS / ORDER INFO

Item #	Order Code	UPC Code	Input Amps @ 120V/277V	Lumens	Wattage	LPW	Equivalent Wattage*	DLC ID	Case Qty
F-FL/13/50K/KN/BZ-67	74185	751338017863	0.10/0.04	1,474	13	113	50-70W MH	PQF47CV6	1/24
F-FL/30/50K/KN/BZ-67	74183	751338017825	0.24/0.10	3,307	30	110	70-150W MH	PBWN5AVR	1/12
F-FL/50/50K/KN/BZ-67	74179	751338017825	0.40/0.18	5,562	50	111	150-250W MH	---	1/12
F-FL/50/50K/TR/BZ-67	74181	751338022812	0.40/0.18	5,562	50	111	150-250W MH	PTGX5XGH	1/12

NOMENCLATURE

Example: **F-FL/13/50K/KN/BZ**

F=Fixture / FL=Flood / 13=13W / 50K=5000K / KN=Knuckle Mount / BZ=Bronze finish
TR=Trunnion Mount

*Equivalent wattage dependent on fixture, reflectance and lumen maintenance of lamp

Specifications are subject to change without prior notice. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

FIVE (5) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED Outdoor Fixtures shall be free from defects of material and workmanship for a period of five (5) years from the date of purchase. TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com