

LED Lamps

Performance Series Globe



Highest Quality of Light

Topaz's Performance Series LED Globe lamps combine our latest LED-energy saving technology with our highest color rendering of >90 CRI. A high quality, long lasting alternative to traditional incandescent globes, these powerful lamps are ENERGY STAR® Certified and meet the requirements of California's Title 20 regulations. Ideal for use in bathrooms, vanities, and other decorative applications.

FEATURES

- 90 CRI provides exceptional color rendering
- Compliant with California Title 20, Tier 2 requirements
- 3000K model supports California Title 24, Part 6 requirements for high efficacy LED light source
- Dimmable down to 5% of total light output
- Approximately 90% energy savings over incandescent lamps
- ENERGY STAR Certified

APPLICATIONS

- Bathroom vanity lighting, decorative and task lighting
- Residential, hospitality, and retail





Job Name/Title: _____ Catalog Number _____

Contractor: _____ Notes: _____

LED Lamps Performance Series Globe

OVERVIEW

Input Voltage, Frequency: 120V, 60Hz

Power Factor/THD %: >0.9/<20%

CRI: >90

Average Rated Life (L70): 25,000 Hours

Location Rating: Damp Location

Ambient Operating Temperature: -4°F to 113°F

Lens Type: Shatter-resistant plastic



ORDER INFO

Catalog Number	Order Code	UPC	Watts	CCT (Kelvin)	PK-QTY	MOL (A)	MOD (B)	Weight
LG25/4/930/D-46	73394	751338033900	4W	3000K	1/6/24	4.3"	3.2"	.16 lbs
LG25/4/940/D-46	73395	751338033917	4W	4000K	1/6/24	4.3"	3.2"	.16 lbs

DIMENSIONS

SPECIFICATIONS

Catalog Number	Input Amps	Lumens	Lumens Per Watt	CBCP (cd)	Beam Angle	Base	Replacement Watts	Dimmable ¹	Enclosed Fixture Rating ²	ENERGY STAR [®]
LG25/4/930/D-46	50mA	360	90	-	170°	E26	40W	Y	Suitable	Y
LG25/4/940/D-46	50mA	360	90	-	170°	E26	40W	Y	Suitable	Y

ENERGY SAVINGS

	LED Watts	Incandescent Watts	Energy Saving, Watts	Yearly Savings	5 Year Savings
Based on 6 hours/day and .11¢/kwhr	4W	40W	36W	\$8.67	\$43.35

NOMENCLATURE

Example: LG25/4/927/D-46

LG25

LED Lamp
G25 Shape

4

Wattage

9XX

90 CRI and:

2700K CCT (Soft White)

3000K CCT (Warm White)

4000K CCT (Cool White)

5000K CCT (Daylight)

D

Dimmable

NOTES:

¹Dimming - This lamp is designed to be compatible with most leading-edge or incandescent style rotary or slide type dimmers. (Dimming range 100% - 5%) Performance may vary depending on dimmer.

²Suitable for enclosed fixtures, provided the ambient temperature inside the fixture does not exceed 113°F

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

This product comes with a 5 year free replacement warranty from the date of purchase. For more information on the limited warranty visit www.topaz-usa.com.

Specifications subject to change without notice. ©2019 Topaz Lighting Corp.