

High-Power LED PAR

LP16/6/27K/D-46

LED PAR16 Lamp



- Dimmable down to 5%*
- Advanced Optics & Thermal Management
- Ideal for track lighting
- Suitable for use in enclosed fixtures

| | |
|---------------------------|-----------------|
| Catalog Number | LP16/6/27K/D-46 |
| Order Code | 79676 |
| UPC | 751338005266 |
| Wattage | 6.5W |
| Input Voltage | 120 |
| Shape | PAR16 |
| Base | E26 Medium |
| Beam Spread | 40° |
| CRI | 80 |
| CCT | 2700K |
| Initial Lumens | 500 |
| Average Rated Life | 25,000 |
| MOL | 2.85" |
| Equivalent Wattage | 60W |
| Warranty | 5 years |

Not for sale in California.

Specifications are subject to change without prior notice.

*Compatible with most leading edge or incandescent style dimmers



Revised July 2020