



Southwire™

FLEXIBLE STEEL CONDUIT COILS

FEATURES

- Corrosion resistant
- Smooth interior for easy wire pull through
- Easy to follow contours
- Crush resistant
- Solid wood reel attached with nylon threaded bolts
- 3/8"–2" available on reels

APPLICATION

- For use as an electrical raceway in close quarters requiring extra flexibility

STANDARD MATERIAL

- Steel construction

STANDARD FINISH

- Hot dip galvanized zinc coating



5201

PART #	SIZE	FEET/ COIL	MASTER QTY.	WEIGHT/ CASE (LBS.)	INSIDE DIAMETER		OUTSIDE DIAMETER	
					MIN.	MAX.	MIN.	MAX.
5200	3/8"	100'	100	15	.374"	.376"	.555"	.571"
5250TZ	3/8"	250'	250	37	.374"	.376"	.555"	.571"
5201	1/2"	100'	100	21	.618"	.634"	.85"	.866"
5202	3/4"	100'	100	25	.827"	.846"	1.043"	1.063"
5203	1"	100'	100	45	1.039"	1.059"	1.28"	1.299"
5203C50	1"	50'	50	24	1.039"	1.059"	1.28"	1.299"
5204	1-1/4"	50'	50	24	1.319"	1.343"	1.512"	1.535"
5205	1-1/2"	50'	50	30	1.496"	1.52"	1.827"	1.85"
5205C25	1-1/2"	25'	25	16	1.496"	1.52"	1.827"	1.85"
5206	2"	25'	25	19	2.047"	2.075"	2.335"	2.362"
5207	2-1/2"	25'	25	26	2.52"	2.559"	2.913"	2.953"
5208	3"	25'	25	31	3.071"	3.110"	3.465"	3.504"
5209	3-1/2"	25'	25	34	3.504"	3.551"	3.909"	3.957"
5210	4"	25'	25	34	4.094"	4.154"	4.449"	4.508"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.