

PLL40

PLL40/50-39

40 Watt Plug-in CFL Lamp

- *Minimum starting temp 50°F*
- *Up to 75% Energy Savings; lasts 10X as long as traditional incandescents*
- *2 year limited warranty*
- *TCLP Compliant*



| | |
|---------------------------|---------------------|
| Item # | PLL40/50-39 |
| Product Code | 78560 |
| UPC Code | 751338076259 |
| Watts | 40 |
| Lamp Shape | PL-Long Twin Tube |
| Base | 4-Pin Plug-in, 2G11 |
| CRI | 82 |
| Color Temp | 5000K |
| Initial Lumens | 3,150 |
| Average Rated Life | 12,000 |
| Mercury Content | 2.7MG |
| MOL | 22.6" |
| Warranty | 2 years |

Specifications are subject to change without prior notice.

