



Job Name/Title: \_\_\_\_\_ Catalog Number \_\_\_\_\_

Contractor: \_\_\_\_\_ Notes: \_\_\_\_\_

## LED Lamps Indoor Reflector - Performance Series BR30



### High-Powered Performance

Topaz's Performance Series LED BR30 Reflector lamps combine our latest LED-energy saving technology with our highest color rendering of >90 CRI. A high quality, long lasting alternative to traditional incandescent and halogen floods, these powerful lamps are ENERGY STAR® Certified and meet the requirements of California's Title 20 regulations. Ideal for use in track lighting, recessed downlighting & floodlight applications.

### FEATURES

- 90 CRI provides exceptional color rendering
- Dimmable down to 5% of total light output
- Approximately 90% energy savings over halogen reflectors
- ENERGY STAR Certified
- T20: Can be used to comply with California Energy Commission's Lighting Appliance Efficiency Regulations
- T24 JA8: 2700K, 3000K, and 4000K models can be used to comply with California Energy Commission's High Efficacy LED light source requirements

### SUGGESTED APPLICATIONS

- Track lighting, recessed downlighting
- Residential, multi-family, and office buildings





Job Name/Title: \_\_\_\_\_ Catalog Number \_\_\_\_\_

Contractor: \_\_\_\_\_ Notes: \_\_\_\_\_

## LED Lamps Indoor Reflectors - Performance Series BR30

### GENERAL SPECIFICATIONS

**Input Voltage, Frequency:** 120V, 60Hz  
**Power Factor, THD %:** >0.9, <20%  
**CRI:** 90  
**Functional Life (L70):** 25,000 Hours  
**Location Rating:** Damp Location  
**Ambient Operating Temperature:** -4°F to 113°F  
**Lens Type:** Shatter-resistant plastic



### ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Wattage	CCT (Kelvin)	PK-QTY	MOL (A)	MOD (B)	Weight
LBR30/8/927/D-46	73336	751338033856	7.5W	2700K	1/6	5.2"	3.7"	.18 Lbs.
LBR30/8/930/D-46	73337	751338033863	7.5W	3000K	1/6	5.2"	3.7"	.18 Lbs.
LBR30/8/940/D-46	73338	751338033870	7.5W	4000K	1/6	5.2"	3.7"	.18 Lbs.
LBR30/8/950/D-46	73339†	751338033887	7.5W	5000K	1/6	5.2"	3.7"	.18 Lbs.

### DIMENSIONS

† Not for sale in residential new construction in California.

### SPECIFICATIONS

Catalog Number	Input Amps	Lumens	Lumens Per Watt	CBCP (cd)	Beam Angle	Base	Replacement Wattage	Dimmable <sup>1</sup>	Enclosed Fixture Rating	ENERGY STAR <sup>®</sup>
LBR30/8/927/D-46	75mA	650	87	220	105°	E26	65W	Y	Not Suitable	Y
LBR30/8/930/D-46	75mA	650	87	220	105°	E26	65W	Y	Not Suitable	Y
LBR30/8/940/D-46	75mA	650	87	220	105°	E26	65W	Y	Not Suitable	Y
LBR30/8/950/D-46	75mA	650	87	220	105°	E26	65W	Y	Not Suitable	Y

### ENERGY SAVINGS

	LED Wattage	Incandescent Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
<b>Based on 6 hours/day and \$0.11/kWh</b>	7.5W	65W	57W	\$13.73	\$17.35

### NOMENCLATURE

Example: LBR30/8/927/D

<b>LBR30</b> LED Lamp BR30 Shape	<b>8</b> Wattage	<b>9XX</b> 90 CRI and: 2700K CCT (Soft White) 3000K CCT (Warm White) 4000K CCT (Cool White) 5000K CCT (Daylight)	<b>D</b> Dimmable
--	---------------------	---	----------------------

### NOTES:

<sup>1</sup>Dimming - This lamp is designed to be compatible with most leading-edge or incandescent style rotary or slide type dimmers. (Dimming range 100% - 5%) Performance may vary depending on dimmer. For an up to date dimmer list visit [www.topaz-usa.com/led-dimmer-compatibility](http://www.topaz-usa.com/led-dimmer-compatibility).

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

This product comes with a 5 year free replacement warranty from the date of purchase. For more information on the limited warranty visit [www.topaz-usa.com](http://www.topaz-usa.com).

Specifications subject to change without notice.

Revised July 2020