



Southwire™

PULLING ROPE

Cable pulling rope designed for high breaking strength with low stretch.

- High strength low stretch
- Excellent resistance to UV rays, chemicals and abrasions
- Excellent balance
- Factory spliced pulling eye at each end
- Polyester double braid
- 9/16" diameter rope recommended for use with the M3K cable puller
- 5/8" diameter rope recommended for use with the M6K cable puller
- 7/8" diameter rope recommended for use with the XD10 cable puller



HEAVY DUTY
SUPERIOR BREAKING STRENGTH,
LOW STRETCH, UV RESISTANT

COMPOSITE DOUBLE BRAID
THE DOUBLE BRAID WEAVE
PROVIDES ENHANCED STRENGTH &
INCREASED PULLING CAPABILITY

READY TO PULL
FACTORY SPLICED PULLING
EYE AT EACH END

MODEL #	STOCK #	DIAMETER (INCHES)	"BREAKING STRENGTH (LBS.)"	LENGTH (FT.)
P-963	56823501	9/16	16,000	300
P-966	56823601	9/16	16,000	600
P-583	56823701	5/8	18,000	300
P-586	56823901	5/8	18,000	600
P-589	57791201	5/8	18,000	900
P-786	56824001	7/8	31,000	600
P-789	57991301	7/8	31,000	900
P-7812	56824101	7/8	31,000	1200

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2021 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.