# **SERIES 2600 THE BIG LIFT**

# **APPLICATIONS**

- 10' or 15' (3-4.6 m)
- 1,100 lbs (500 kg) capacity
- 2 speed winch
- Travels through doorway
- · Legs fold for compact storage
- · Rolls into vehicles
- Adjustable steering level handle
- Legs unlock with plunger pin and fold up for storage. Roller wheels under each leg for ease of moving lift in stored position
- Aluminum pulleys enclosed to prevent cable from coming off
- Mast hold bar for horizontal transportation. Hold down bar can be reshaped if bent.
- Rugged two speed which makes lifting heavy loads a snap
- Mast roller wheels help to roll lift into vehicles
- Nifty lifting hook for crane use

# **ACCESSORIES**

## **ADJUSTABLE STEERING HANDLE**

Adjustable steering handle that pops out of way with push buttom.

### **OUTRIGGER LOCKING MECHANISM**


Locks legs both in stored or operating position. Note: Outriggers standard on 15' model, optional on 10' model.

### REVERSED FORK

Forks can quickly be reversed with plunger pins.

#### **FORK EXTENSIONS**

With push of a button, optional fork extensions extend forks extra 8" (20 cm). Extensions store in forks. Extension capacity 450 lbs (205 kg).



PART #	DESCRIPTION	LENGTH STOWED	WIDTH STOWED	HEIGHT STOWED	WEIGHT LIFT	10' SAFETY BRAKES	15' SAFETY BRAKES	FORK EXTENSION
783065	2610 The Big Lift	34" (86.4 cm)	31.5 " (80 cm)	76.5" (194.3 cm)	292 lbs (132.5 kg)	783882		783163
783067	2615 The Big Lift	34" (86.4 cm)	31.5 " (80 cm)	76.5" (194.3 cm)	346 lbs (157 kg)		783883	783163

