



# Southwire™

## SECURITY LIGHTS

### 32W MOTION ACTIVATED WHITE LED SECURITY LIGHT

- 180-Degree Motion Detection with up to 45ft Range
- 2-Head LED Light Fixture
- Polycarbonate Lens
- Delay Time: Test/1min/5min/10min
- 3200 Lumens | 120Vac | 32 Watts
- 6000K Color Temperature



### 34W MOTION ACTIVATED WHITE LED SECURITY LIGHT

- 240-Degree Motion Detection with up to 45ft Range
- 3-Head LED Light Fixture
- Polycarbonate Lens
- Delay Time: Test/1min/5min/10min
- 3800 Lumens | 120Vac | 34 Watts
- 6000K Color Temperature



### 240-DEGREE SOLAR MOTION ACTIVATED WHITE LED SECURITY LIGHT

- 240-Degree Motion Detection with up to 45ft Range
- 3-Head LED Light Fixture
- Polycarbonate Lens
- Delay Time: Test/30s/60s/120s
- 1800 Lumens | Solar | 2000mAh Li-ion Battery
- 6000K Color Temperature



MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
L17SL252MW	032886745706	32W Motion Activated White LED Security Light	6.5"	7.1"	7.7"	2.4 lbs.
L17SL303MW	032886743030	34W Motion Activated White LED Security Light	6.5"	7.9"	9.6"	3.2 lbs.
L17SOL183MW	032886745744	240-Degree Solar Motion Activated White LED Security Light	6.9"	8.3"	9.4"	3.4 lbs.

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2020 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.