

LED Linear Lighting

13W 6"U-Bend Frosted LED Retrofit T8 w/Internal Driver

Features

- Electronic IS ballast compatible*
- Extremely long life and energy efficient
- No mercury
- Full light around bend
- Polycarbonate construction

Specs

- 13W
- 120-277V
- 80 CRI
- 160° beam angle
- 50,000 Average Rated Life
- -20°C/-4°F Minimum Start Temperature

Applications

- Commercial offices, retail, schools and hospitality



Catalog Number	Product Code	UPC Code	Color Temp	Lumens	Wattage	Case Qty
L4T8E/U6/835/13F-70	74161	751338016385	3500K	1,950	13	1/12
L4T8E/U6/840/13F-70	74162	751338016392	4000K	2,000	13	1/12
L4T8E/U6/850/13F-70	74163	751338016408	5000K	2,000	13	1/12

Specifications are subject to change without prior notice.

*Works with most instant start ballasts, please see www.topaz-usa.com for compatibility.