



Southwire™

SIMPush™ RIGID CONDUIT BODIES

T TYPE - ALUMINUM

FEATURES

- Gasket NBR Nitrile
- No need to thread conduit
- Works with threaded or non-threaded RMC, IMC, GRC, ARC and rigid stainless steel
- Copper free aluminum, powder coat
- Reusable, tested for up to 100 removal cycles
- Watertight, concrete tight, direct burial rated

APPLICATIONS

- Allows access for inspection, pulling and maintenance

STANDARD MATERIAL

- Copper free aluminum

CERTIFICATIONS

- UL Listed, 514B, IP66, NEMA 4X



R-TB-050

STOCK #	MODEL #	SIZE	QUANTITY PER BAG	OVERALL PRODUCT DIMENSIONS			ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
				HEIGHT	WEIGHT	LENGTH		
RETAIL POLY-BAG PACKAGING								
65080101	R-TB-050	1/2"	1	6.801"	2.208"	2.83"	R-RT-1P	---
65080201	R-TB-075	3/4"	1	7.56"	2.463"	3.09"	R-RT-1P	---
65080301	R-TB-100	1"	1	8.60"	2.969"	3.328"	R-RT-2P	---
STOCK #	MODEL #	SIZE	QUANTITY PER BOX	HEIGHT	WEIGHT	LENGTH	ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
CONTRACTOR PACK								
65080102	R-TB-050W	1/2"	4	6.801"	2.208"	2.83"	R-RT-1P	---
65080202	R-TB-075W	3/4"	4	7.56"	2.463"	3.09"	R-RT-1P	---
65080302	R-TB-100W	1"	4	8.60"	2.969"	3.328"	R-RT-2P	---
65080502	R-TB-125W	1-1/4"	3	10.82"	3.976"	4.53"	R-RT-2P	---
65080602	R-TB-150W	1-1/2"	3	10.88"	4.192"	4.56"	R-RT-3P	---
65080702	R-TB-200W	2"	1	12.99"	5.041"	5.31"	R-RT-3P	---

Rev. 0, 06/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.