

BX, FLEX CONNECTORS STRAIGHT - SQUEEZE TYPE WITH INSULATED THROAT - MALLEABLE IRON

FEATURES

Squeeze type straight with insulated throat

APPLICATION

- Indoor use only
- In a dry location, use to connect flexible metallic conduit and steel AC cable to a steel outlet box, load center or other metal enclosure
- Suitable for: 1/2" steel flexible conduit, #14/2 metal conduit and #4-2 wire steel armored cable, 3/4" steel flexible metal conduit and #6-3 wire steel armored cable, 1" steel and reduced wall steel flexible metal conduit and #2-2 wire steel armored cable and 1-1/4" - 4" steel flexible metal conduit

STANDARD MATERIAL

Malleable iron

STANDARD FINISH

Zinc plated

CERTIFICATIONS


• cULus

PART #	CONDUIT SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B (MIN. – MAX.)	C	SCREWS
151MI	1/2"	25	250	12	.94"	.78" – .94"	.50"	1
152MI	3/4"	25	250	19	1.13"	.91" – 1.08"	.50"	1
153MI	1"	10	100	26	1.19"	1.28" - 1.44"	.56"	1
154MI	1-1/4"	10	100	39	1.25"	1.44" - 1.63"	.63"	1
155MI	1-1/2"	5	50	66	1.88"	1.63" - 1.88"	.69"	1
156MI	2"		20	105	2"	2.19" – 2.38"	.75"	1
157MI	2-1/2"		10	150	2.06"	2.70" - 2.95"	.94"	2
158MI	3"		2	200	2.25"	3.13" - 3.50"	.94"	2
159MI	3-1/2"		1	500	3.56"	3.72" - 4"	1.25"	2
160MI	4"		1	700	3.69"	4.06" - 4.44"	1.25"	2



151MI





Rev. 0. 02/23