



Southwire™

FLEXIBLE STEEL CONDUIT REELS

FEATURES

- Corrosion resistant
- Smooth interior for easy wire pull through
- Easy to follow contours
- Crush resistant
- Solid wood reel attached with nylon threaded bolts
- 3/8"–4" available in coils

APPLICATION

- For use as an electrical raceway in close quarters requiring extra flexibility

STANDARD MATERIAL

- Steel construction

STANDARD FINISH

- Hot dip galvanized zinc coating



5202R

| PART # | SIZE | FEET/ REEL | MASTER QTY. | WEIGHT/ CASE (LBS.) | INSIDE DIAMETER | | OUTSIDE DIAMETER | |
|----------|--------|---------------|----------------|------------------------|-----------------|--------|------------------|--------|
| | | | | | MIN. | MAX. | MIN. | MAX. |
| 5200R | 3/8" | 1000' | 1000 | 159 | .374" | .376" | .555" | .571" |
| 5201R | 1/2" | 500' | 500 | 80 | .618" | .634" | .85" | .866" |
| 5201RL | 1/2" | 1000' | 1000 | 160 | .618" | .634" | .85" | .866" |
| 5202R | 3/4" | 300' | 300 | 48 | .827" | .846" | 1.043" | 1.063" |
| 5202R500 | 3/4" | 500' | 500 | 80 | .827" | .846" | 1.043" | 1.063" |
| 5203R | 1" | 200' | 200 | 99 | 1.039" | 1.059" | 1.28" | 1.299" |
| 5203R300 | 1" | 300' | 300 | 150 | 1.039" | 1.059" | 1.28" | 1.299" |
| 5204R | 1-1/4" | 200' | 200 | 104 | 1.319" | 1.343" | 1.512" | 1.535" |
| 5204R400 | 1-1/4" | 400' | 400 | 52 | 1.319" | 1.343" | 1.512" | 1.535" |
| 5205R | 1-1/2" | 100' | 100 | 63 | 1.496" | 1.52" | 1.827" | 1.85" |
| 5206R | 2" | 100' | 100 | 81 | 2.047" | 2.075" | 2.335" | 2.362" |

Rev. 0, 02/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.