

LED Outdoor Fixture Accessories Twist-Lock Photocells



480V



120-277V

FEATURES

- Built-in surge protection
- Waterproof clear polycarbonate lens
- UV stabilized polypropylene enclosure
- Solid brass 3-pin prongs
- 3 Year warranty

GENERAL SPECIFICATIONS

- Ambient Temp:** -40° to 158°F
- Lifetime:** 5,000 Cycles
- Frequency:** 50/60 Hz
- Fail Mode:** Fail On
- Rated Loading:** 1,000W Tungsten / 1800VA Ballast

SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Input Voltage	Housing Color	ANSI	Turn-on level	Turn-off level	Case QTY
WD-PC/TL/120-277	72711	751338033771	120-277V	Blue	C136.10	6 Lux	50 Lux	50-Pk
WD-PC/TL/480	72722	751338033788	480V	Yellow	C136.10	16 Lux	24 Lux	50-Pk

NOMENCLATURE

Example: WD-PC/TL/120-277

WD Wiring Device	PC Photocell	TL Twist-Lock	120-277 480 Voltage
----------------------------	------------------------	-------------------------	---



THREE (3) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED fixture accessories shall be free from defects of material and workmanship for a period of three (3) years from date of purchase. TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED fixtures that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice. ©2019 Topaz Lighting Corp.