

LED Omnidirectional A19



True Omnidirectional Light Distribution

Topaz LED Omnidirectional A19 lamps are ideal for both residential and commercial settings including down lights, wall sconces, ceiling fans, table and floor lamps. Dimmable down to 10% for additional energy savings and ambiance control.

FEATURES

- 220° beam spread
- 85% energy savings compared to incandescent lamps
- Suitable for use in totally enclosed luminaires
- Long life - up to 10X longer than traditional incandescents
- RoHS compliant and mercury free
- Plastic lens material provides shatter protection

SUGGESTED APPLICATIONS

- Fan lights, decorative, recessed, task lighting
- Residential, hospitality, retail, restaurants, commercial





Job Name/Title: _____ Catalog Number _____
 Contractor: _____ Notes: _____

LED Omnidirectional A19

GENERAL SPECIFICATIONS

Input Voltage: 120V
Average Rated Life: 25,000 Hours
CRI: 80

THD: <15%
Beam Angle: 220°
Ambient Operating Temp: -4°F to 104°F

SPECIFICATIONS / ORDER INFO

Catlog Number	Order Code	UPC	Replacement Wattage	Wattage	Base	CCT	Lumens	LPW	MOL	Pl-Qty	Dimmable	ENERGY STAR
LA19/6W/27K/D-46	74370	751338024069	6W	40W	E26	2700K	480	80	4.35"	1/6/24	Y	Y
LA19/6W/30K/D-46	74371	751338024106	6W	40W	E26	3000K	480	80	4.35"	1/6/24	Y	Y
LA19/6W/40K/D-46	74372	751338024120	6W	40W	E26	4000K	480	80	4.35"	1/6/24	Y	Y
LA19/6W/50K/D-46	74373	751338024137	6W	40W	E26	5000K	480	80	4.35"	1/6/24	Y	Y
LA19/9W/27K/D-46	74374	751338024144	9.8W	60W	E26	2700K	800	82	4.35"	1/6/24	Y	Y
LA19/9W/30K/D-46	74375	751338024151	9.8W	60W	E26	3000K	800	82	4.35"	1/6/24	Y	-
LA19/9W/40K/D-46	74376	751338024168	9.8W	60W	E26	4000K	800	82	4.35"	1/6/24	Y	Y
LA19/9W/50K/D-46	74377	751338024182	9.8W	60W	E26	5000K	800	82	4.35"	1/6/24	Y	Y
LA19/11W/27K/D-46	74378	751338024199	11W	75W	E26	2700K	1,100	100	4.35"	1/6/24	Y	Y
LA19/11W/30K/D-46	74379	751338024229	11W	75W	E26	3000K	1,100	100	4.35"	1/6/24	Y	Y
LA19/11W/40K/D-46	74380	751338024236	11W	75W	E26	4000K	1,100	100	4.35"	1/6/24	Y	Y
LA19/11W/50K/D-46	74381	751338024243	11W	75W	E26	5000K	1,100	100	4.35"	1/6/24	Y	Y
LA19/15W/27K/D-46	74382	751338024250	15W	100W	E26	2700K	1,600	107	4.65"	1/6/24	Y	Y
LA19/15W/30K/D-46	74383	751338024274	15W	100W	E26	3000K	1,600	107	4.65"	1/6/24	Y	Y
LA19/15W/40K/D-46	74384	751338024298	15W	100W	E26	4000K	1,600	107	4.65"	1/6/24	Y	Y
LA19/15W/50K/D-46	74385	751338024304	15W	100W	E26	5000K	1,600	107	4.65"	1/6/24	Y	Y
LA19/9W/27K/GU24D	74386	751338024311	9.8W	60W	GU24	2700K	800	82	4.35"	1/6/24	Y	Y
LA19/9W/30K/GU24D	74387	751338024328	9.8W	60W	GU24	3000K	800	82	4.35"	1/6/24	Y	Y
LA19/9W/40K/GU24D	74388	751338024335	9.8W	60W	GU24	4000K	800	82	4.35"	1/6/24	Y	Y
LA19/11W/30K/GU24D	74389	751338024342	11W	75W	GU24	3000K	1,100	100	4.35"	1/6/24	Y	Y

Not for sale in California.

NOMENCLATURE

Example: LA19/6W/27K/D

LA19 = LED A19 Shape / 6W = 6 Watt / 27K = 2700K / D = Dimmable
 / 9W = 9 Watt / 30K = 3000K / GU24D = GU24 Base, Dimmable
 / 11W = 11 Watt / 40K = 4000K
 / 15W = 15 Watt / 50K = 5000K

ENERGY SAVINGS

	LED Wattage	Halogen/ Incandescent Wattage	Energy Saving, Watts	Yearly Saving, Fixture	5 Year Cost Savings
Based on 5 hours/day and \$0.11/kWh					
LA19/6W/XXK/D	6W	40W	34W	\$6.83	\$34.13
LA19/9W/XXK/D	9.8W	60W	50W	\$10.04	\$50.19
LA19/11W/XXK/D	11W	75W	64W	\$12.85	\$64.24
LA19/15W/XXK/D	15W	100W	85W	\$17.06	\$85.32
LA19/9W/XXK/GU24D	9.8W	60W	50W	\$10.04	\$50.19
LA19/11W/30K/GU24D	11W	75W	64W	\$12.85	\$64.24

NOTES:

Suitable for enclosed fixtures. This device is not intended for use with emergency exits.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

FIVE (5) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED lamps shall be free from defects of material and workmanship for a period of five (5) years from the date of purchase. Based on 12 hours of use per day, TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice.

Revised March 2022