



**Southwire™**

# FLEXIBLE LIQUIDTIGHT CONDUIT

## METALLIC - REEL

### FEATURES

- Crush and corrosion resistant steel core for lasting mechanical protection
- EF PVC jacket is oil and sunlight resistant
- Smooth interior for easy wire pull through

### APPLICATION

- For use in damp or wet locations, suitable for commercial and industrial use
- Non UL

### STANDARD MATERIAL

- EF PVC jacketed steel core coil on reel



**6101R**

PART #	SIZE	FEET REEL	MASTER QTY.	WEIGHT/ CASE (LBS.)	INSIDE DIAMETER		OUTSIDE DIAMETER	
					MIN.	MAX.	MIN.	MAX.
6100R	3/8"	1000'	1000'	182	.484"	.504"	.689"	.709"
6101R	1/2"	1000'	1000'	296	.622"	.642"	.819"	.839"
6102R	3/4"	500'	500'	148	.815"	.835"	1.032"	1.051"
6103R	1"	200'	200'	96	1.032"	1.055"	1.287"	1.315"
6104R	1-1/4"	200'	200'	192	1.37"	1.394"	1.63"	1.661"
6105R	1-1/2"	100'	100'	79	1.579"	1.598"	1.866"	1.902"
6105R150	1-1/2"	150'	150'	120	1.579"	1.598"	1.866"	1.902"
6106R	2"	100'	100'	96	2.02"	2.043"	2.339"	2.374"

Rev. 0, 01/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.