



Cleaner, quicker steel punch dies.

- **HEAVY DUTY CUTTING**  
Cuts through 10 gauge steel (3.5mm) as well as aluminum, fiberglass and plastics




- **HEAVY DUTY CUTTING**  
Cuts through 10 gauge stainless steel (3.5mm) as well as aluminum, fiberglass and plastics

- **QUICKER SMOOTHER CUT**  
Will not bow panel or leave jagged edges



- **QUICKER SMOOTHER CUT**  
Will not bow panel or leave jagged edges





### Specifications

#### MILD STEEL

\* Drive Unit Not Included

MODEL #	STOCK #	DESCRIPTION	CONDUIT & PIPE SIZE	HOLE SIZE ACTUAL"	MM	CAPACITY M.S. GA
MPK050	56826301	MAX PUNCH® 1/2" conduit size cutter	1/2"	.89	23	10
MPC50	56827301	MAX PUNCH® 1/2" conduit size cup	1/2"	.89	23	10
MPK075	56826401	MAX PUNCH® 3/4" conduit size cutter	3/4"	1.12	28	10
MPC75	56827401	MAX PUNCH® 3/4" conduit size cup	3/4"	1.12	28	10
MPK0100	56826501	MAX PUNCH® 1" conduit size cutter	1"	1.36	35	10
MPC100	56827501	MAX PUNCH® 1" conduit size cup	1"	1.36	35	10
MPK0125	56826601	MAX PUNCH® 1 1/4" conduit size cutter	1 1/4"	1.70	43	10
MPC125	56827601	MAX PUNCH® 1 1/4" conduit size cup	1 1/4"	1.70	43	10
MPK0150	56826701	MAX PUNCH® 1 1/2" conduit size cutter	1 1/2"	1.95	50	10
MPC150	56827701	MAX PUNCH® 1 1/2" conduit size cup	1 1/2"	1.95	50	10
MPK0200	56826801	MAX PUNCH® 2" conduit cutter	2"	2.42	62	10
MPC200	56827801	MAX PUNCH® 2" conduit cup	2"	2.42	62	10
MPK0250	56826901	MAX PUNCH® 2 1/2" conduit cutter	2 1/2"	2.92	74	10
MPC250	56828001	MAX PUNCH® 2 1/2" conduit cup	2 1/2"	2.92	74	10
MPK0300	56827001	MAX PUNCH® 3" conduit cutter	3"	3.55	90	10
MPC300	56828101	MAX PUNCH® 3" conduit cup	3"	3.55	90	10
MPK0350	56827101	MAX PUNCH® 3 1/2" conduit cutter	3 1/2"	4.04	103	10
MPC350	56828201	MAX PUNCH® 3 1/2" conduit cup	3 1/2"	4.04	103	10
MPK0400	56827201	MAX PUNCH® 4" conduit cutter	4"	4.54	115	10
MPC400	56828301	MAX PUNCH® 4" conduit cup	4"	4.54	115	10
MPO2	56825701	MAX PUNCH® Small Die Set 1/2"-2" in case*	1/2"-2"	.89-2.42	23-62	10
MP03	56825801	MAX PUNCH® Large Die Set 2 1/2"-4" in case*	2 1/2"-4"	2.92-4.54	74-115	10

#### STAINLESS STEEL

MODEL #	STOCK #	DESCRIPTION	CONDUIT & PIPE SIZE	HOLE SIZE ACTUAL"	MM	CAPACITY S.S. GA
MPK050PRO	56826301	MAX PUNCH® Cutter for Stainless Steel 1/2"	1/2"	.89	23	10
MPC50PRO	56827301	MAX PUNCH® Cup for Stainless Steel 1/2"	1/2"	.89	23	10
MPK075PRO	56826401	MAX PUNCH® Cutter for Stainless Steel 3/4"	3/4"	1.12	28	10
MPC75PRO	56827401	MAX PUNCH® Cup for Stainless Steel 3/4"	3/4"	1.12	28	10
MPK0100PRO	56826501	MAX PUNCH® Cutter for Stainless Steel 1"	1"	1.36	35	10
MPC100PRO	56827501	MAX PUNCH® Cup for Stainless Steel 1"	1"	1.36	35	10
MPK0125PRO	56826601	MAX PUNCH® Cutter for Stainless Steel 1 1/4"	1 1/4"	1.70	43	10
MPC125PRO	56827601	MAX PUNCH® Cup for Stainless Steel 1 1/4"	1 1/4"	1.70	43	10
MPK0150PRO	56826701	MAX PUNCH® Cutter for Stainless Steel 1 1/2"	1 1/2"	1.95	50	10
MPC150PRO	56827701	MAX PUNCH® Cup for Stainless Steel 1 1/2"	1 1/2"	1.95	50	10
MPK0200PRO	56826801	MAX PUNCH® Cutter for Stainless Steel 2"	2"	2.42	62	10
MPC200PRO	56827801	MAX PUNCH® Cup for Stainless Steel 2"	2"	2.42	62	10
MPK0250PRO	56826901	MAX PUNCH® Cutter for Stainless Steel 2 1/2"	2 1/2"	2.92	74	10
MPC250PRO	56828001	MAX PUNCH® Cup for Stainless Steel 2 1/2"	2 1/2"	2.92	74	10
MPK0300PRO	56827001	MAX PUNCH® Cutter for Stainless Steel 3"	3"	3.55	90	10
MPC300PRO	56828101	MAX PUNCH® Cup for Stainless Steel 3"	3"	3.55	90	10
MPK0350PRO	56827101	MAX PUNCH® Cutter for Stainless Steel 3 1/2"	3 1/2"	4.04	103	10
MPC350PRO	56828201	MAX PUNCH® Cup for Stainless Steel 3 1/2"	3 1/2"	4.04	103	10
MPK0400PRO	56827201	MAX PUNCH® Cutter for Stainless Steel 4"	4"	4.54	115	10
MPC400PRO	56828301	MAX PUNCH® Cup for Stainless Steel 4"	4"	4.54	115	10
MPO2PRO	56825701	MAX PUNCH® Small Die Set 1/2"-2" in case*	1/2"-2"	.89-2.42	23-62	10
MP03PRO	56825801	MAX PUNCH® Large Die Set 2 1/2"-4" in case*	2 1/2"-4"	2.92-4.54	74-115	10

