

MINI-ROLL JACK

STANDARD FEATURES

- 1/2 to 36" (1.2 to 91 cm) pipe capacity
- 3,500 lbs (1,580 kg) weight capacity
- Roller adjusts from either side
- Quick change roller heads
- Brake to lock loads for layout
- No need for wedges
- Carbon steel or stainless steel roller heads
- Rubber wheel roller head (1,200 lbs | 550 kg capacity)
- Ball transfer roller head (1,000 lbs | 450 kg capacity carbon or stainless steel balls)
- Bar stock head (2,000 lbs | 900 kg capacity two position roller for containment or non-containment of material)



| PART NO. | DESCRIPTION | WEIGHT |
|----------|--|------------------|
| 785280 | Mini Roll with Roller Wheels | 23 lbs (10.4 kg) |
| 785281 | Mini Roll with Ball Transfer Heads | 22 lbs (10 kg) |
| 785282 | Mini Roll with Rubber Wheels | 22 lbs (10 kg) |
| 785283 | Mini Roll with Roller Wheels | 23 lbs (10.4 kg) |
| 785284 | Mini Roll with Bar Stock Head | 31 lbs (14.1 kg) |
| 785288 | Mini Roll with S.S. Ball Transfer Heads | 23 lbs (10.4 kg) |
| 785285 | Mini Roll – Base Only | 15 lbs (6.8 kg) |
| 783151 | Q.C.R.H. with Roller Wheels | 8 lbs (3.6 kg) |
| 783152 | Q.C.R.H. with Rubber Wheels | 7 lbs (3.2 kg) |
| 783153 | Q.C.R.H. with Roller Wheels | 8 lbs (3.6 kg) |
| 783154 | Q.C.R.H. with Ball Transfer Head | 7 lbs (3.2 kg) |
| 783155 | Q.C.R.H. with Bar Stock Head | 16 lbs (7.2 kg) |
| 783159 | Q.C.R.H. with Stainless Steel Ball Transfer Head | 8 lbs (3.6 kg) |