



WE'VE EXPANDED YOUR OPTIONS

WOBBLELIGHT® 32 SERIES

The Wobblelight® LED V-Series, has the same great patented, self-righting technology with a new look. Still ideal for applications requiring temporary high output lighting for areas up to 75 feet diameter. This new look features an integrated carry handle into the body, LED panel technology and an integrated cord to give the unit a suitable for wet locations rating. The V2 model also has a covered receptacle for interlinking units together.

50,000 HOURS LED LIFE

LINK UP TO 6 UNITS

IP54 RATED

NO WARM UP TIME

INTEGRATED LEDS
NO BULBS TO SHATTER

LIGHTS UP TO 60 FT.



WOBBLELIGHT® 36 SERIES

The patented self-righting Wobblelight®; is ideal for applications requiring temporary high-output lighting in areas from 15 to 75 feet diameter. Bright and dependable, the Wobblelight®; delivers maximum light output in a highly durable and portable package with no hot surfaces.

20,000 HOURS BULB LIFE

LINK UP TO 3 UNITS

HAS TO WARM UP
PRIOR TO USAGE

400 WATT METAL HALIDE BULB

LIGHTS UP TO 75 FT.



MODEL #	UPC#	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT	WARRANTY
111301LED	786625001096	Wobblelight® V2 150 Watt LED Work Light	33"	16.5"	16.5"	37 lbs	1 Year
111104	786625136903	Wobblelight® 36" 400 Watt Metal Halide	26.5"	18.75"	14.75"	34 lbs	1 Year

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.