

LED Round High Bay POWER & CCT SELECTABLE



SUGGESTED APPLICATIONS

- Warehouses
- Manufacturing facilities
- Gymnasiums
- Retail stores

FEATURES

- Choose from three wattage and two CCT choices for up to 6 possible configurations
- 90° Optical lens designed to minimize glare and discomfort
- Aluminum alloy construction, IK08 impact rated polycarbonate lens
- Includes J-hook, 3' safety cable, 6' power and dimming cord
- Optional accessories include plug and play microwave motion sensor, J-Box kit, and emergency battery backup



LED Round High Bay POWER & CCT SELECTABLE

MOTION SENSOR PRE-PROGRAMMED SETTINGS

Brightness	Sensitivity	Hold Time	Daylight Threshold	Standby Dimming Level	Standby Dimming Period
100%	100%	10 Min	Off	10%	1 Min

ENERGY SAVINGS

Based on 12 hours/day and \$0.11 kWh

Catalog Number	LED Lamp Wattage	HID Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
HBC-150W-PCTS-BL	100W	250W	150W	\$72	\$361
	120W	320W	200W	\$96	\$482
	150W	400W	250W	\$120	\$602
HBC-150W-PCTS-WH	100W	250W	150W	\$72	\$361
	120W	320W	200W	\$96	\$482
	150W	400W	250W	\$120	\$602
HBC-200W-PCTS-BL	150W	400W	250W	\$120	\$602
	180W	400W-600W	420W	\$202	\$1,012
	200W	600W	400W	\$193	\$964
HBC-200W-PCTS-WH	150W	400W	250W	\$120	\$602
	180W	400W-600W	420W	\$202	\$1,012
	200W	600W	400W	\$193	\$964

DIMENSIONS/WEIGHTS

Catalog Number	(A)	(B)	Weight
HBC-150W-PCTS-BL	11.81"	6.50"	5.1 Lbs.
HBC-150W-PCTS-WH	11.81"	6.50"	5.1 Lbs.
HBC-200W-PCTS-BL	14.17"	7.44"	8.4 Lbs.
HBC-200W-PCTS-WH	14.17"	7.44"	8.4 Lbs.

