

PURGE BUDDY

Inflatable pipe stopper with schrader valve.

APPLICATIONS

- Inexpensive purge dam
- Air tight pipe sealing
- Stoppage of odors and debris
- Low pressure testing
- Heat resistant to 100°C / 210°F
- 2" - 36" pipe capacity
- Heavy duty polyester / cotton impregnated with canvas material
- Latex bladder
- Pull loops for inside of the pipe
- 1.5 m / 4.8 ft inflation hose
- Inflates with standard bicycle pump
- Vent loops to secure argon hose



PART NO.	DESCRIPTION	PIPE SIZE	MAX ID	MAX INFLATION PRESSURE
786080	2" Purge Buddy	50 mm	55mm	15 PSI / 1.03 Bar
786081	3" Purge Buddy	75 mm	84 mm	15 PSI / 1.03 Bar
786082	4" Purge Buddy	100 mm	112 mm	15 PSI / 1.03 Bar
786083	5" Purge Buddy	125 mm	138 mm	15 PSI / 1.03 Bar
786084	6" Purge Buddy	150 mm	168 mm	15 PSI / 1.03 Bar
786085	8" Purge Buddy	200 mm	224 mm	14 PSI / 0.96 Bar
786086	10" Purge Buddy	250 mm	276 mm	10 PSI / 0.68 Bar
786087	12" Purge Buddy	300 mm	324 mm	8 PSI / 0.55 Bar
786088	14" Purge Buddy	350 mm	368 mm	7 PSI / 0.48 Bar
786089	16" Purge Buddy	400 mm	417 mm	6.5 PSI / 0.45 Bar
786090	18" Purge Buddy	450 mm	481 mm	6 PSI / 0.41 Bar
786091	20" Purge Buddy	500 mm	520 mm	5 PSI / 0.34 Bar
786092	22" Purge Buddy	550 mm	559 mm	4.5 PSI / 0.31 Bar
786093	24" Purge Buddy	600 mm	637 mm	4 PSI / 0.27 Bar
786094	28" Purge Buddy	700 mm	737 mm	3.5 PSI / 0.24 Bar
786095	30" Purge Buddy	750 mm	788 mm	3.25 PSI / 0.22 Bar
786096	32" Purge Buddy	800 mm	813 mm	3.25 PSI / 0.22 Bar
786097	36" Purge Buddy	900 mm	943 mm	3 PSI / 0.2 Bar