

## LED Red Exit & Emergency Combo

NYC APPROVED



### Glare Free LED Adjustable Round Lamp Heads

City of New York approved heavy duty emergency exit and lighting combo unit offers safety and security in a modern, easy to install design. This self-contained unit meets the requirements of all five boroughs of New York City. Emergency unit is OSHA compliant and contains a long lasting Ni-Cad battery backup for essential illumination during a power outage.

### FEATURES

- 120/277V dual voltage operation
- Red EXIT letters - 8" height and 1" stroke with glare-free adjustable LED lamp heads
- 20-gauge steel housing with white powder coating
- Wall or side mounting capability
- Test switch and AC supply indicator
- Removeable knockout chevron directional arrows
- Battery backup with accessible test button for 90 minutes of illumination during a power outage
- Suitable for damp locations
- Meets UL924, NFPA 101, NEC, and OSHA standards

### APPLICATIONS

- Emergency lighting for office, industrial, retail and other public spaces





Job Name/Title: \_\_\_\_\_ Catalog Number \_\_\_\_\_

Contractor: \_\_\_\_\_ Notes: \_\_\_\_\_

## LED Red Exit & Emergency Combo NYC APPROVED

### GENERAL SPECIFICATIONS

- Input Voltage:** 120/277V (dual voltage)
- Frequency:** 50/60 Hz
- CRI:** 80
- Avg. Rated Life:** 500 uses
- Damp Location**
- Construction:** 20 Gauge steel, white finish
- Mounting:** Wall or side mount
- Recharge time:** 24 hrs
- Runtime:** >/= 90 minutes
- Battery Backup:** Two 3.6V, 800mA
- Ambient Operating Temperature:** 50°F to 104°F



**AC Supply Indicator LED Light**

**Battery Backup, Push to Test Button**



**20-Gauge Steel Housing**

**Red EXIT Letters  
8" Height, 1" Stroke**

**1W Glare-Free Adjustable Round Lamp Heads**

**Removeable Knockout Chevron Directional Arrows**

### SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Number of Lamp Head	Wattage	Lumens	Lumens Per Watt	Number of Faces	Dimensions	Unit Weight	Pk-Qty
ESC/LED/RW/2H-NYC	71234	751338039179	2	1 W per head	100 per head	100	Single/Double	14.5" x 2.8" x 16.43"	8.27 Lbs.	3-PK
ESC/LED/RW-NYC	75140	751338033498	3	1W per head	100 per head	100	Single/Double	14.6" x 2.3" x 16.5"	10.36 Lbs.	3-PK

Not for sale in California.

### NOMENCLATURE

**Example: ESC/LED/RW/2H-NYC**

**ESC** = Emergency Combo / **LED** = LED / **RW** = Red Letters, White Housing / **2H** = 2 Head **NYC** = New York City Approved  
/ **Blank** = 3 Head

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Fixture may not be compatible with all dimmers. Visit [www.topaz-usa.com](http://www.topaz-usa.com) for up-to-date dimmer compatibility information. Specifications subject to change without notice.

Revised February 2021