



# Southwire™

## BENDMAX™ POWER BENDER

Power bender 3/4" - 2" EMT, IMC, and Rigid conduit.

- Easily adjustable to ergonomic working height
- 2 degree leveling adjustment
- Industrial-grade DC drive, and electrical components
- Push cart mounted platform
- Total lock casters

**PROGRAMMABLE SPRINGBACK  
INCORPORATED INTO DIGITAL  
READOUT**

**LARGE ANALOG PROTRACTOR  
FOR ACCURATE BENDS**

**BACKLIT DIGITAL DISPLAY**

**BENDS IN BOTH THE VERTICAL  
AND HORIZONTAL PLANES**

**ELEVATION TRAVEL INDICATOR**



SCAN TO SEE MORE

MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
PB2000	59840601	BENDMAX™ Power Bender	38"	30"	50"	600 lbs.

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2025 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.