



Southwire™

M500CX4

Coax Continuity Tester/Mapper

THE M500CX4 SPEEDS TROUBLESHOOTING AND INSTALLATION BY TESTING AND IDENTIFYING UP TO FOUR CABLE TV REMOTE WALL OUTLETS AT A TIME. INCLUDES FOUR COLOR CODED REMOTES.



Southwire™

TOOLS & EQUIPMENT

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-SWT00LS
(855-798-6657)



Scan code to see more
Southwiretools.com



Southwire™

M500CX4

Continuity Tester for Data Cable



- EASY-TO-UNDERSTAND LED DISPLAY
- TEST PATCH CABLES OR INSTALLED CABLES
- IDENTIFY UP TO FOUR COAX CABLE REMOTE LOCATIONS - INCLUDES 4 COLOR-CODED ID REMOTES
- DOUBLE-MOLDED HOUSING FOR DURABILITY AND GRIP
- AUTO POWER-OFF



⚠ WARNING: Never use on live circuits.

⚠ ADVERTENCIA: Nunca a use en circuitos con corriente

M500CX4 CONTINUITY TESTER FOR DATA CABLE

Max. testing length	10,000ft (3km) maximum
Operating temperature	14°F to 122°F (-10° to 50°)
Storage temperature	-4 to 140°F (-20° to 60°)
Battery	Four LR44 Batteries
Case dimensions	5.4 in. x 1.26 in. x 0.98 in. (13.7 cm x 3.2cm x 2.5cm)
Weight	3.14oz (89g)

INCLUDES

Coax Continuity Tester/Mapper, 4 ID Remotes, 4 1.5 VLR44 Batteries

⚠ WARNING: Never use on live circuits.



Southwire™

TOOLS & EQUIPMENT

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-SWTOOLS
(855-798-6657)



Scan code to see more
Southwiretools.com