



Southwire™

METAL BARB CABLE TIES

CABLE TIES WITH A STAINLESS STEEL BARB FOR SUPERIOR WIRE MANAGEMENT

FEATURES

- Stainless Steel Barb provides a secure and reliable self-locking mechanism
- Safely and easily secures wire bundles and harness components
- cULus Listed per UL Standard 62275, Type 21 or 21S
- Suitable for Air Handling Spaces (AH-2)
- Available in lengths from 4" to 30" with tensile strength from 18lbs to 120lbs



STRONG, DURABLE 304 STAINLESS STEEL BARB CONSTRUCTION FOR ENHANCED DURABILITY AND STRENGTH

INFINITE ADJUSTABILITY ALONG BUNDLE RANGE WITH SECURE SELF-LOCKING MECHANISM

MANUFACTURED USING POLYAMIDE 6.6 SUITABLE FOR INDOORS (NATURAL) AND OUTDOORS (UV RESISTANT BLACK)

OPERATING TEMPERATURE MINIMUM -40°F TO MAXIMUM 185°F



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

METAL BARB CABLE TIES

PART #	TENSILE STRENGTH (LBS.)	COLOR	LENGTH	MAX. BUNDLE DIAMETER	BAG QTY.	CASE QTY.
BR4MMP0-C	18	UV BLACK	4.0"	0.8"	100	1,000
BR4MMP9-C	18	NATURAL	4.0"	0.8"	100	1,000
BR6MMP0-C	18	UV BLACK	6.3"	1.56"	100	1,000
BR6MMP9-C	18	NATURAL	6.3"	1.56"	100	1,000
BR8MMP0-C	18	UV BLACK	8.0"	2.06"	100	1,000
BR8MMP9-C	18	NATURAL	8.0"	2.06"	100	1,000
BR5IMP0-C	40	UV BLACK	5.5"	1.30"	100	1,000
BR5IMP9-C	40	NATURAL	5.5"	1.30"	100	1,000
BR8IMP0-C	40	UV BLACK	8.0"	2.06"	100	1,000
BR8IMP9-C	40	NATURAL	8.0"	2.06"	100	1,000
BR12IMP0-C	40	UV BLACK	11.8"	3.30"	100	1,000
BR12IMP9-C	40	NATURAL	11.8"	3.30"	100	1,000
BR15IMP0-C	40	UV BLACK	14.5"	4.17"	100	1,000
BR15IMP9-C	40	NATURAL	14.5"	4.17"	100	1,000
BR8SMP0-C	50	UV BLACK	8.0"	1.94"	100	1,000
BR8SMP9-C	50	NATURAL	8.0"	1.94"	100	1,000
BR12SMP0-C	50	UV BLACK	11.8"	3.18"	100	1,000
BR12SMP9-C	50	NATURAL	11.8"	3.18"	100	1,000
BR15SMP0-C	50	UV BLACK	14.5"	4.07"	100	1,000
BR15SMP9-C	50	NATURAL	14.5"	4.07"	100	1,000
BR8LMP0-L	120	UV BLACK	8.6"	2.25"	50	500
BR8LMP9-L	120	NATURAL	8.6"	2.25"	50	500
BR12LMP0-L	120	UV BLACK	11.8"	3.25"	50	500
BR12LMP9-L	120	NATURAL	11.8"	3.25"	50	500
BR14LMP0-L	120	UV BLACK	14.5"	4.07"	50	500
BR14LMP9-L	120	NATURAL	14.5"	4.07"	50	500
BR18LMP0-L	120	UV BLACK	18.0"	5.13"	50	500
BR18LMP9-L	120	UV BLACK	18.0"	5.13"	50	500
BR24LMP0-L	120	UV BLACK	24.4"	7.14"	50	500
BR24LMP9-L	120	NATURAL	24.4"	7.14"	50	500
BR30LMP0-L	120	UV BLACK	30.0"	3.31"	50	500
BR30LMP9-L	120	NATURAL	30.0"	3.31"	50	500

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.