



LED MR16 Dimmers & Transformers Compatibility



6W MR16 Non-DIM -- Transformers Compatibility



●Compatible ; ○Flickering

Transformers Brand	Transformers Item#	Qty of MR16 Lamp					
		1	2	3	4	5	6
HATCH	RS12-60M	●	●	●	●	●	●
HATCH	RS12-30M-LED	●	●	●	●	●	●
HATCH	RS12-60M-LED	●	●	●	●	●	○
DALS	ET6012IV	●	●	●	●	●	○
HATCH	RS12-80M	●	●	●	●	●	●
LIGHTECH	LET60LW	●	●	●	●	●	●
DALS	ET8012iV	●	●	●	●	●	●
HATCH	RS12-15M-LED	●	●	●	●	●	●
	ET-MZ-60	●	●	●	●	●	●
TEMO LITE	TRA-50	●	●	●	●	●	●
DALS	ET15012IV	●	●	●	●	●	●
LIGHTECH	E61883	●	●	●	●	●	●
EUROFASE	0086	●	●	○	○	●	●
DALS	1060T	○	●	●	●	●	●
CONSTRALITA	AC1048	●	●	●	●	●	●
TEMO LITE	TRA-50	●	●	●	●	●	●
B+L	FX95100	●	●	●	●	●	●
WAC	E-N-1260-R-AR	●	●	●	○	●	●
WAC	E-N-1275-R-AR	●	●	●	●	●	●
REATOR	FORCE LINE	●	●	●	○	○	○
STNDARD	31017STD	●	●	●	●	●	●
MINI MAGG	B01742	●	●	●	●	●	●
EUROFASE	0089	●	●	●	●	●	●
DALS	ET8012LV	●	●	●	●	●	●
HATCH	RS12-30M-LED	●	●	●	●	●	●

7W MR16 Non-DIM -- Transformers Compatibility



●Compatible ; ○Flickering

HATCH	RS12-60M	●	●	●	●	●	○
HATCH	RS12-30M-LED	●	●	●	●	●	●
HATCH	RS12-60M-LED	●	●	●	●	●	●
DALS	ET6012IV	●	●	●	●	●	●
HATCH	RS12-80M	●	●	●	●	●	●
LIGHTECH	LET60LW	●	●	●	●	●	●
DALS	ET8012IV	●	●	●	●	●	●
HATCH	RS12-15M-LED	●	●	●	●	●	●
	ET-MZ-60	●	●	●	●	●	●
TEMO LITE	TRA-50	●	●	●	●	●	●
DALS	ET15012IV	●	●	●	●	●	●
LIGHTECH	E61883	●	●	●	●	●	●
EUROFASE	0086	●	●	○	○	●	●
DALS	1060T	○	●	●	●	●	●
CONSTRALITA	AC1048	●	●	●	●	●	●
TEMO LITE	TRA-50	●	●	●	●	●	●
B+L	FX95100	●	●	●	●	●	●
WAC	E-N-1260-R-AR	●	●	●	○	●	●
WAC	E-N-1275-R-AR	●	●	●	●	●	●
REATOR	FORCE LINE	●	●	●	●	●	●
STNDARD	31017STD	●	●	●	●	●	●
MINI MAGG	B01742	●	●	●	●	●	●
EUROFASE	0089	●	●	●	●	●	●
DALS	ET8012LV	●	●	●	●	●	●
HATCH	RS12-30M-LED	●	●	●	●	●	●

7W MR16 DIM - Dimmers & Transformers Compatibility



●Compatible ; ○Flickering

Dimmers item #	Transformers Brand	Transformers Item#	Testing result						
			1(Pmax/Pmin)	2	3	4	5	6	
LUTRON NELV-450	HATCH	RS12-60M	●(7.7/3.3)	○	○	○	○	○	
	HATCH	RS12-30M-LED	●(7.34/2.2)	●	●	●	●	●	
	HATCH	RS12-60M-LED	●(7.33/2.3)	●	●	●	●	●	
	DALS	ET6012IV	○ (7.8/2.8)	○	○	○	○	○	
	HATCH	RS12-80M	●(7.9/3.2)	○	○	○	○	○	
	LIGHTECH	LET60LW	● (7.56/2.5)	●	●	●	●	●	
	DALS	ET8012iV	○ (7.74/3)	○	○	○	○	○	
	HATCH	RS12-15M-LED	● (7.32/2.5)	●	●	●	●	●	
			ET-MZ-60	○ (7.9/1.1)	○	○	○	○	○
	TEMO LITE		TRA-50	● (7.8/2.1)	○	○	○	○	○
	DALS		ET15012IV	○ (8.1/2.6)	○	○	○	○	○
	LIGHTECH		E61883	○ (7.3/4)	○	○	●	●	●
	EUROFASE		0086	○ (8.0/1.35)	○	○	●	●	●
	DALS		1060T	○ (8/2.1)	○	○	○	○	○
	CONSTRALITA		AC1048	●(7.7/2.45)	●	●	●	●	●
	TEMO LITE		TRA-50	○ (7.8/2.3)	○	○	○	○	○
	B+L		FX95100	●(7.3/2.2)	●	●	●	●	●
	WAC		E-N-1260-R-AR	○ (8.1/1.9)	○	○	○	○	○
	WAC		E-N-1275-R-AR	○ (8.3/0.8)	○	○	○	○	○
	REATOR		FORCE LINE	●(8.1/1.7)	○	○	○	○	○
	STNDARD		31017STD	●(7.5/4.1)	●	●	●	●	●
	MINI MAGG		B01742	○ (7.6/2.6)	○	○	○	○	○
	EUROFASE		0089	○ (7.8/2.5)	○	○	○	○	○
	DALS		ET8012LV	○ (7.5/3.5)	○	○	○	○	○
HATCH		RS12-30M-LED	●(7.6/1.9)	●	●	●	●	●	

7W MR16 DIM - Dimmers & Transformers Compatibility



●Compatible ; ○Flickering

Dimmers item #	Transformers Brand	Transformers Item#	Testing result						
			1(Pmax/Pmin)	2	3	4	5	6	
LUTRON-DVELV-300P	HATCH	RS12-60M	●(7.4/1)	○	○	○	○	○	
	HATCH	RS12-30M-LED	●(7.2/0.6)	●	●	●	●	●	
	HATCH	RS12-60M-LED	●(7.2/0.7)	●	●	●	●	●	
	DALS	ET6012IV	○ (7.6/0.8)	○	○	○	○	○	
	HATCH	RS12-80M	○ (7.9/0.93)	○	○	○	○	○	
	LIGHTECH	LET60LW	● (7.4/0.8)	●	●	●	●	●	
	DALS	ET8012iV	○ (7.6/0)	○	○	○	○	○	
	HATCH	RS12-15M-LED	● (7.2/0.7)	●	●	●	●	●	
			ET-MZ-60	○ (7.9/0.17)	○	○	○	○	○
	TEMO LITE	TRA-50	● (7.6/0.76)	○	○	○	○	○	
	DALS	ET15012IV	○ (7.9/0.6)	○	○	○	○	○	
	LIGHTECH	E61883	○ (7.1/1.5)	○	○	●	●	●	
	EUROFASE	0086	○ (8/0.1)	○	○	○	●	●	
	DALS	1060T	○ (7.9/0.2)	○	○	○	○	○	
	CONSTRALITA	AC1048	○ (7.6/0.6)	○	○	○	○	○	
	TEMO LITE	TRA-50	○ (7.7/0.5)	○	○	○	○	○	
	B+L	FX95100	●(7.3/0.78)	●	●	●	●	●	
	WAC	E-N-1260-R-AR	○ (8.1/0.1)	○	○	○	○	○	
	WAC	E-N-1275-R-AR	○ (8.4/0)	○	○	○	○	○	
	REATOR	FORCE LINE	●(8/0.4)	○	○	○	○	○	
	STNDARD	31017STD	●(7.5/1.15)	●	●	●	●	●	
	MINI MAGG	B01742	○ (7.6/1)	○	○	○	○	○	
	EUROFASE	0089	○ (7.5/0)	○	○	○	○	○	
	DALS	ET8012LV	○ (7.5/0.42)	○	○	○	○	○	
HATCH	RS12-30M-LED	●(7.3/1.4)	●	●	●	●	●		

7W MR16 DIM - Dimmers & Transformers Compatibility



●Compatible ; ○Flickering

Dimmers item #	Transformers Brand	Transformers Item#	Testing result						
			1(Pmax/Pmin)	2	3	4	5	6	
LUTRON-SELV-300P	HATCH	RS12-60M	○ (7.5/1.02)	○	○	○	○	○	
	HATCH	RS12-30M-LED	●(7.3/0.6)	●	●	●	●	●	
	HATCH	RS12-60M-LED	●(7.27/0.65)	●	●	●	●	●	
	DALS	ET6012IV	○ (7.7/0.77)	○	○	○	○	○	
	HATCH	RS12-80M	○ (7.9/0.9)	○	○	○	○	○	
	LIGHTECH	LET60LW	● (7.47/0.82)	●	●	●	●	●	
	DALS	ET8012iV	○ (7.6/0.65)	○	○	○	○	○	
	HATCH	RS12-15M-LED	● (7.24/0.66)	●	●	●	●	○	
			ET-MZ-60	○ (7.9/0)	○	○	○	○	○
	TEMO LITE	TRA-50	● (7.66/0.78)	○	○	○	○	○	
	DALS	ET15012IV	○ (7.9/0.71)	○	○	○	○	○	
	LIGHTECH	E61883	○ (7.18/1.5)	○	○	●	●	●	
	EUROFASE	0086	○ (8/0)	○	○	●	●	●	
	DALS	1060T	○ (8/0)	○	○	○	○	○	
	CONSTRALITA	AC1048	○ (7.6/0.7)	○	○	○	○	○	
	TEMO LITE	TRA-50	○ (7.8/0.62)	○	○	○	○	○	
	B+L	FX95100	●(7.3/0.83)	●	●	●	●	●	
	WAC	E-N-1260-R-AR	○ (8.3/0)	○	○	○	○	○	
	WAC	E-N-1275-R-AR	○ (8.4/0)	○	○	○	○	○	
	REATOR	FORCE LINE	●(8/0.35)	○	○	○	○	○	
	STNDAR	31017STD	●(7.56/1.2)	●	●	●	●	●	
	MINI MAGG	B01742	○ (7.6/1.6)	○	○	●	●	●	
	EUROFASE	0089	○ (7.7/0)	○	○	○	○	○	
	DALS	ET8012LV	○ (7.5/0.3)	○	○	○	○	○	
	HATCH	RS12-30M-LED	●(7.6/1.16)	●	●	●	●	●	